

## Garant

### Circular saw blade, wood, alternating teeth universal, Blade Ø D: 300mm



#### Order data

Order number	584075 300
GTIN	4045197220905
Item class	51S

#### Description

##### Version:

**Tipped with carbide inserts**, precision version with high-strength blade, noise damped. Generously dimensioned carbide teeth allow multiple re-grinding.

##### Application:

For circular, cross-cut, compound, and mitre saws.

**Universal** circular saw blade with long tool life and low noise, **unaffected by nails**. For **all wood types** and difficult materials in the building trade, including aluminium sections

##### Note:

**Further circular saw blades can be found in Group 17.**

Bore Ø: 30 mm

Drive holes number/Ø/pitch circle: 2/7/42 and 2/9/46 and 2/10/60 mm

Number of teeth: 48

Width of cut B: 3.2 mm

#### Technical description

Number of teeth	48
Blade Ø D	300 mm

Bore Ø	30 mm
Width of cut B	3.2 mm
Drive holes number/Ø/pitch circle	2/7/42 and 2/9/46 and 2/10/60 mm
Type of product	Circular saw blade