

Garant
Precision circlip pliers, Type: A2

Order data

Order number	719870 A2
GTIN	4045197504111
Item class	71B

Description
Version:

Forged grip and joint. Precision made tips of special steel, special precision profile and pressed into the body.

Pliers, blacked. Ground head. Plastic coated handles. Joint with **integral opening spring**. **Form A – straight jaws**.

Advantage:

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

Application:

For fitting and removing circlips.

Standard:

DIN 5254 A und B – für Außensicherungsringe.

Use of circlip pliers: Outer ring, straight

overall length: 180 mm

for external circlips \varnothing : 19 - 60 mm

Tip \varnothing : 1.8 mm

Technical description

Shape	A
for external circlips \varnothing	19 - 60 mm
Tip \varnothing	1.8 mm

overall length	180 mm
Standard	DIN 5254 A
Use of circlip pliers	Outer ring, straight
Jaw shape	straight
Handle	plastic coated
Material	Special steel
Material of point	Special steel
Surface	black
with over-expansion guard	no
Joint with integral opening spring	yes
Handle with self-grip mechanism	no
Exchangeable points	no
Type of product	Circlip Pliers