

Garant
DNMG 150404, Type: HB7010-1


Order data

Order number	250767 HB7010-1
GTIN	4045197949073
Item class	21G

Description

DNMG 150404 HB7010-1 Grade: HB7010-1
 Chip breaker: SM
 Tolerance: M
 Cutting depth a_p : 0.5 - 5 mm
 Feed f : 0.2 - 0.5 mm/rev.
 Cutting speed v_c main application: 120 - 440 m/min

Technical description

Cutting conditions	continuous
Corner radius	0.4 mm
Tool material	Carbide
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Main application	P
Cutting speed v_c main application	120 - 440 m/min
Chip breaker	SM

Feed f	0.2 - 0.5 mm/rev.
Grade	HB7010-1
Cutting depth a_p	0.5 - 5 mm
ISO code indexable insert	DNMG 150404
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning