

Garant
DNMG 150408, Type: HB7010-1


Order data

Order number	250768 HB7010-1
GTIN	4045197949110
Item class	21G

Description

DNMG 150408 HB7010-1 Grade: HB7010-1
 Chip breaker: SM
 Tolerance: M
 Cutting depth a_p : 0.5 - 5 mm
 Feed f : 0.2 - 0.5 mm/rev.
 Cutting speed v_c main application: 120 - 440 m/min

Technical description

Main application	P
Tool material	Carbide
Feed f	0.2 - 0.5 mm/rev.
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Cutting conditions	continuous
Grade	HB7010-1
Cutting speed v_c main application	120 - 440 m/min

Chip breaker	SM
Corner radius	0.8 mm
Cutting depth a_p	0.5 - 5 mm
ISO code indexable insert	DNMG 150408
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning