

Garant
DNMG 150404, Type: HB7035-1


Order data

Order number	250767 HB7035-1
GTIN	4045197949097
Item class	21G

Description

DNMG 150404 HB7035-1 Grade: HB7035-1
 Chip breaker: SM
 Tolerance: M
 Cutting depth a_p : 0.5 - 5 mm
 Feed f : 0.2 - 0.5 mm/rev.
 Cutting speed v_c main application: 100 - 320 m/min

Technical description

Grade	HB7035-1
Cutting conditions	heavily interrupted
Chip breaker	SM
Cutting depth a_p	0.5 - 5 mm
Main application	P
Tool material	Carbide
Feed f	0.2 - 0.5 mm/rev.

Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Cutting speed v_c main application	100 - 320 m/min
Corner radius	0.4 mm
ISO code indexable insert	DNMG 150404
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning