

HOLEX**All-steel lever clamp, Jaw capacity: 300mm****Order data**

Order number	860650 300
GTIN	4045197494443
Item class	82C

Description**Version:**

Beam / fixed jaw made of bright drawn steel, moving jaw of forged steel, each hardened and electro galvanised. Clamping lever with self-locking ratchet clamping mechanism. Opens by releasing the ratchet. Movable pressure pad, clamping lever powder coated.

Application:

For **fast** and easy **clamping with high clamping pressure**.

Cross section of the slide rail: 25×12 mm

Throat: 140 mm

Weight: 2.31 kg

Technical description

Cross section of the slide rail	25×12 mm
Jaw capacity	300 mm
Throat	140 mm
Weight	2.31 kg

Type of product

Clamp