

**Garant**
**GARANT Master Tap machine tap Form B, ALTiX, M: M1,6**

**Order data**

Order number	132721 M1,6
GTIN	4045197984098
Item class	11I

**Description**
**Version:**

**Universal taps**, designed for use in a wide spectrum of materials with high process reliability.

- **HSS-E-PM tool material for a high degree of wear resistance.**
- **Reduced coefficient of friction due to the new high-performance coating.**
- **Special geometry for optimum swarf evacuation.**

Corresponds to **ISO 2X/6HX**.

Thread type: M

Tool material: HSS E PM

Standard: DIN 371

Tolerance class: ISO 2X 6HX

Thread pitch: 0.35 mm

Overall length L: 40 mm

Shank  $\varnothing D_s$ : 2.5 mm

Shank square  $\square$ : 2.1 mm

Tapping hole  $\varnothing$ : 1.25 mm

**Technical description**

Number of clamping slots	2
Thread pitch	0.35 mm
Tool material	HSS E PM
Standard	DIN 371
Shank $\varnothing D_s$	2.5 mm
Tolerance class	ISO 2X 6HX

Tapping hole $\varnothing$	1.25 mm
Number of cutting edges Z	2
Overall length L	40 mm
Shank square $\square$	2.1 mm
Thread $\varnothing$	1.6 mm
Thread depth	4.8 mm
Thread type	M
Thread size	M1.6
Coating	AlTiX
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Series	Master Tap
Type of product	Tap

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable	30 m/min	N
Aluminium (short chipping)	suitable	35 m/min	N
Alu > 10% Si	suitable	20 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	30 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	30 m/min	P

Steel < 900 N/mm <sup>2</sup>	suitable	25 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	12 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	8 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	10 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	8 m/min	M
GG(G)	suitable	20 m/min	K
CuZn	suitable	20 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		