



## Husqvarna AMG 3200

AMG 3200 is a petrol-powered drive unit for Husqvarna AA and AZ mechanical concrete vibrators. The fuel-efficient, rubber-mounted Honda GX 160 petrol engine delivers reliable power all workday long in all conditions, and is easy to service if needed. A sturdy coupling with quick release allows for problem-free power transmission to the flexible shaft.

### Low fuel consumption

The built-in fuel tank provides hours of uninterrupted work.

### Easy to service

The engine is easy to service with simple access to all service points.

### Engine protection

The robust frame with side covers protects the rubber-mounted engine from external forces.

### Quick release

A sturdy coupling with quick release makes it easy to attach and release the flexible shaft.

## PXM\_FEATURES

- Engine protection
- Easy to service
- Low fuel consumption
- Quick release

### Technical Specifications

| ENGINE                       |                     |
|------------------------------|---------------------|
| Motor/engine manufacturer    | Honda               |
| Motor/engine model           | GX160               |
| Output power                 | 3.6 kW              |
| Max engine/motor             | 3000 rpm            |
| Fuel tank volume             | 3.1 l               |
| Exhaust emissions (CO2 EU V) | 757 g/kWh           |
| Fuel tank volume             | 0.82 gal (US)       |
| DIMENSIONS                   |                     |
| Weight                       | 15 kg               |
| SOUND AND NOISE              |                     |
| Sound level                  | 75.7 dB(A)          |
| Sound power level, measured  | 75.7 dB(A)          |
| PACKAGING                    |                     |
| Packaging length             | 1200 mm             |
| Packaging width              | 800 mm              |
| Packaging height             | 650 mm              |
| Packaging volume             | 624 dm <sup>3</sup> |

## ACCESSORIES



HUSQVARNA AA  
967 85 73-01



HUSQVARNA AA  
967 85 74-01



HUSQVARNA AA  
967 85 75-01



HUSQVARNA AA  
967 85 76-01



HUSQVARNA AA  
967 85 77-01