

# TEMPORARY JUMPER CABLE

Single Conductor, 90°C Dry Locations Only, 15kV EPR Insulation, Non-Shielded



Image not to scale. See Table 1 for Dimensions

## CONSTRUCTION:

**Conductors:** Class A, Compressed, Concentric Lay Stranded Bare Copper per ASTM B3, B8

**Insulation:** Ethylene Propylene Rubber (EPR)

**Assembly:** A conductor shield is applied just under the insulation

## APPLICATIONS AND FEATURES:

Southwire Temporary Jumper cables are intended for use as power leads to by-pass portions of aerial power lines. They are also used in equipment where a non-shielded cable is required.

**Access to these cables are limited to authorized personnel.**

## SPECIFICATIONS:

- ASTM B3, B8

## SAMPLE PRINT LEGEND:

SOUTHWIRE 2 AWG EPR 15KV

**TABLE 1 - WEIGHTS & MEASUREMENTS**

Stock Code	Cond. Size (AWG)	No. of Strands	Insulation Thickness (mils)	Nominal OD (mils)	Nominal Weight (Lbs/Mft)
TBD	2	7	200	683	427
TBD	2/0	7	200	814	700

All dimensions are nominal and subject to nominal manufacturing tolerances



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | [www.southwire.com](http://www.southwire.com)

Copyright © 2016 Southwire Company, LLC. All Rights Reserved



**Southwire®**

OEMCS2016132 DATE: 07/19/16 Rev. 0