

Garant**NC reamer set No. 162900 in a box H7, Number of reamers: 6****Order data**

| | |
|--------------|---------------|
| Order number | 162925 6 |
| GTIN | 4045197994813 |
| Item class | 110 |

Description**Version:**

Version suitable for NC similar to DIN 212 **with straight shank \varnothing** for **standard chucking** especially in **hydraulic chucks** or **high precision collet chucks**. For **highest concentricity** and **process reliability**. **No need to order special collets**. With long flutes and left-hand helix. Even number of teeth with irregular spacing. Size 3 with centring tip, from size 4 with centre holes at both ends.

Reamer manufacturing tolerance to DIN 1420 for H7 hole tolerance field.

Content:

1 pc. each NC reamer: Size 3; 4; 5; 6; 8; 10

Supplied with:

6-piece NC reamer set in a box.

Application for type of drilling: for through holes

Technical description

| | |
|-------------------|-------|
| Number of reamers | 6 |
| Hole tolerance | H7 |
| Tool material | HSS E |

| | |
|----------------------------------|-------------------------|
| Standard | Manufacturer's standard |
| Shank | DIN 1835 A to h6 |
| Application for type of drilling | for through holes |
| Type of product | Phillips bit |

Accessories

| | |
|---|-------------|
| NC reamer H7 Nominal Ø DC mm or inch 3 | 162900 3 |
| NC reamer H7 Nominal Ø DC mm or inch 8 | 162900 8 |
| NC reamer H7 Nominal Ø DC mm or inch 6 | 162900 6 |
| NC reamer H7 Nominal Ø DC mm or inch 10 | 162900 10 |
| NC reamer H7 Nominal Ø DC mm or inch 4 | 162900 4 |
| NC reamer H7 Nominal Ø DC mm or inch 5 | 162900 5 |
| 3-10 | 160100 3-10 |