

# 1 Mil High Temperature Masking Tape with Liner

## PPTWL Series

### RoHS & REACH Compliant

1 Mil High Temperature Masking Tapes with Liner are made of 1 mil thick polyimide film with a PET liner and 1.5 mil thick silicone adhesive. These tapes are reliable and durable with a unique combination of electrical, thermal, chemical, and mechanical properties. 1 Mil High Temperature Masking Tapes are packaged on a 3" core and are 36 yards long.


### Applications

- 3D Printing and Aerospace Assembly
- Automotive Facilities and Electronic Assembly
- Fiber Optics Manufacturing and Solar Panels

### Product Specifications <sup>(1)</sup>

Color	Amber	
Adhesion Type	Silicone	
Film Thickness	2 Mil	ASTM D-3652
Adhesive Thickness	1.5 Mil	
Total Thickness	3.5 Mil	ASTM D-3652
Tensile Strength	30 lbs./in	ASTM D-3759
Elongation	55%	ASTM D-3759
Liner	PET (Polyethylene)	
Dielectric Strength	6,500 volts	ASTM D-149
Operating Temperature	-73°C (-100°F) to 260°C (500°F)	
Length	36 Yards	
Adhesion to Steel	25 Oz./in	ASTM D-3330
Core	3 in. Plastic Core	

<sup>(1)</sup> Specifications are subject to change at any time. If you have any questions, please contact us for the latest update.



Bertech® makes no warranty, representation, or guarantee regarding the information contained herein or the suitability of its this product for any particular purpose, nor does Bertech® assume any liability whatsoever arising out of the application or use of this product. It is ultimately the responsibility of the customer to determine a product's suitability for a particular application.



**Bertech**  
640 Maple Ave  
Torrance, CA 90503  
Phone: (310) 787-0337  
Email: [sales@bertech.com](mailto:sales@bertech.com)  
[www.bertech.com](http://www.bertech.com)

**PRODUCT DATA SHEET**