



Husqvarna DM 540i

Husqvarna DM 540i is a powerful battery drill motor optimised for handheld drilling of diameters up to 75 mm. It can be used in light reinforced concrete for both wet and dry drilling and other suitable materials include bricks and light weight blocks. DM 540i can be used with the DS 150 drill stand for drilling of diameters up to 100 mm and with built-in connectivity, you can easily monitor machine location, runtime, service intervals and receive wireless updates through FOTA (firmware over the air). Power is supplied by BLi-series batteries and the machine is compatible with Husqvarna BLi200/BLi300 batteries. Ease of use and exceptional ergonomic characteristics such as low weight and a well-balanced machine body make it an excellent choice for drilling underneath sinks, in narrow corners or other tight spaces. Other applications include plumbing pipes, electrical sockets, cables, ventilation and air conditioning installations.



Flexible and efficient

Can be used outdoors or indoors, and for wet or dry drilling. Combined with our drill stand, it enables a flexible, efficient working day.



Exceptional ergonomics

Ergonomic design, low weight and a well-balanced machine body deliver easier, more comfortable operation in tight spaces without putting excess strain on your body.

Increased productivity

Without the need for power from the grid or time-consuming equipment set-up procedures, productivity is increased.



Easy to operate and manage

Thanks to a lower rotational energy through a permanent magnetic motor in combination with advanced motor control, the motor stops quickly if the drill gets stuck. This makes it easy to operate and manage the power in the handles created by the stop torque.



PXM_FEATURES

- Increased productivity
- Exceptional ergonomics
- Flexible and efficient
- Easy to operate and manage
- Built-in connectivity
- One battery system
- Smart battery placement
- In-house developed brushless motor provides a high and consistent torque.
- Low maintenance

Technical Specifications	
DRILLING EQUIPMENT	
Drill bit diameter handheld, max	3 in
Drill bit diameter with stand, max	4 in
Recommended drill bit diameter, min	0.59 in
SPECIFICATIONS	
Water pressure, max	43.5 psi
Mounting collar	2.36 in
Spindle thread, inner	G 1/2"
Spindle thread, outer	1 1/4" 7 UNC
TRANSMISSION	
Number of gearbox speeds	2
DIMENSIONS	
Water connector	Gardena Male
Weight	10.8 lbs
Product size length	17.32 in
Product size width	4.33 in
Product size height	10.83 in
SOUND AND NOISE	
Sound power level, guaranteed (LWA)	97 dB(A)
Sound power level, measured	86 dB(A)
Sound pressure level at operators ear	86 dB(A)
PACKAGING	
Packaging length	600 mm
Packaging width	220 mm
Packaging height	400 mm
Packaging volume	52.8 dm ³

ACCESSORIES



HUSQVARNA BATTERY BLI300
967 96 43-02



HUSQVARNA BATTERY BLI200
967 96 41-02



HUSQVARNA BATTERY BLI100
967 96 39-02



HUSQVARNA CHARGER QC500
967 96 50-03



HUSQVARNA CHARGER QC330
967 96 49-03



HUSQVARNA CHARGER QC80F
967 96 48-02



HUSQVARNA INVERTER VI600F
967 96 51-04



HUSQVARNA WT 151
599 58 23-04



HUSQVARNA WT 15i
599 58 24-06



HUSQVARNA WT2GO
598 74 24-01



SLURRY RINGS WSR
593 56 30-01



HUSQVARNA DS 150
966 82 72-02



WHEELBASE DS 250 / 150
541 40 50-89



HUSQVARNA W 250 P
967 70 21-04



HUSQVARNA W 70 P
967 66 47-01



HUSQVARNA S 13
967 66 40-01



HUSQVARNA WL 8i
970 58 49-01



HUSQVARNA WL 8i
970 61 73-01