



APPLIANCE WIRING MATERIAL

Subj.758 Section 1 Page 1199

Issued:1959-08-06

Revised:2013-11-20

Style 1199 Single conductor with extruded insulation

Rating 200 deg C, 600 Vac, Horizontal Flame. Optional
- 80 deg C Oil, Gasoline Resistant.

Conductor 30 AWG - 4/0 AWG, solid or stranded.

Insulation Extruded PTFE.

| <u>Conductor size</u> | <u>Minimum average thickness</u> | <u>Minimum thickness at any point</u> |
|-----------------------|--------------------------------------|---|
| 30-10 AWG | 20 mils | 18 mils |
| 8-2 AWG | 30 mils | 27 mils |
| 1-4/0 AWG | 45 mils | 40 mils |

Standard Appliance Wiring Material UL 758.

Marking General.

Use Internal wiring of appliances and electronic
equipment. Tags may indicate the following:
2500 Volts Peak - For Electronic Use Only.

UL and the UL Logo are trademarks of UL LLC © 2016