

DATE: 10-10-2012
 CS # 2012086
 Revision 1, EKG

PRODUCT SPECIFICATION

TYPE: Flexible Locomotive & Car Equipment Cable (DLO)
 2000 Volt, 90°C
 Heat Resisting Ethylene Propylene Rubber Insulation (EPR)
 Chlorosulfonated Polyethylene Jacket (CSPE) (Hypalon)
 UL Listed Type RHH or RHW-2 2KV per UL 44
 CSA Listed Type RW90 EP 1KV FT-1 per C22.2 No.38
 MSHA Approved P-7K-MSHA

SIZE: 2/0 – 4/0 AWG – One Conductor

I. SCOPE:

This specification covers the minimum construction requirements for single conductor electric cables for use in wiring Locomotive and Car Equipment or similar applications requiring a UL Listed Type RHH/RHW-2 flexible stranded power cable.

These cables are rated at 2000 Volts for use at conductor temperatures up to 90°C in wet or dry locations.

The construction consists of flexible stranded, tin-coated copper conductors insulated with clean stripping Ethylene Propylene Rubber (EPR) insulation and jacketed with Chlorosulfonated Polyethylene (CSPE).

These cables pass the Cold Bend Test at –40°C and may be flexed at temperatures –25°C and warmer.

II. CONSTRUCTION DATA:

SIZE	STRANDING	CONDUCTOR O.D. (INCHES)	INSULATION MIN. AVG. WALL (MILS)	OUTER INSULATION/JACKET		NOMINAL WEIGHT (LBS/MFT)
				MIN. AVG. WALL (MILS)	NOMINAL O.D. (INCHES)	
2/0 AWG	324	0.420	80	45	0.676	532
4/0 AWG	532	0.537	80	65	0.833	822

A. CONDUCTOR:

Tin-coated annealed copper per ASTM B-33 and B-174.

DATE: 10-10-2012
CS # 2012086
Revision 1, EKG

B. INSULATION:

Ethylene Propylene Rubber (EPR) conforming to UL 1581 for Class 28 Table 50.42, UL 44 requirements for RHW and RHW-2, ASTM D-2270 and ICEA S-95-658 Class E-1. It shall be suitable for conductor temperatures up to 90°C in wet or dry locations for continuous use, 130°C for emergency overloads, and 250°C for short circuits.

C. JACKET:

Chlorosulfonated Polyethylene (CSPE) conforming to ICEA S-95-658 Par. 4.1.11 and UL 1581 Table 50.1.

D. SAMPLE PRINT LEGEND:

2/0 AWG TYPE RHH OR RHW-2 2 KV (-40 (D)C) SUN RES FOR
CT USE FT4/IEEE 1202 (UL) E18321 ---A.I.W. CORP. ---
(CSA LOGO) LL8825 RW90 EP 1 KV (-40 (D)C) EP/JKT OIL
RES TC FT4 --- EPR/HYP 2KV DIESEL LOCOMOTIVE CABLE P-
7K-136047-1-MSHA
SEQUENTIAL FOOTAGE MARKS