			DATE	REV	ECN	DESCRIPTION	
<u>PRODUCT</u>	<u>'SPECIFICATION</u>		6/13/2006	А	13131	SPECIFICATION CREATED	
<u>Parent Number:</u> <u>Description:</u>	F04083- 4 61/22 BC SGX per J1127	DIAMETER: 0 TOLERANCE ± : 0					
<u>Stranding:</u>	<u>61/22 BC LHL</u>					NOM WALL: 0.065	
Style	SGX per SAE J1127					MINIMUM WALL: 0.045	
<u>Insulation:</u> <u>Print Legend:</u>	<u>NO PRINT</u>						
Voltage: Per SAE J 1127 this product is intended for use at a nominal system voltage of 60 Volts DC or less in surface vehicle electrical systems.							
Temperature: The Temperature Class Rating is 125C. The Temperature Class rating is defined by SAE as " a class designation based on the retention of mechanical properties after 168 hours of aging at 30C above the temperature class rating". Notes: 1. Paper separator is used between the copper conductor and insulation.							
This product complies with European Directive 2002/95/EC (RoHS) The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Coleman Cable's control all product data presented is for informational purposes only and does not create a binding obligation or liability on Coleman Cable or confer any rights on any customer. The sale of product(s) is conditioned upon acceptance of a purchase order subject to Coleman Cable's standard terms and conditions contained therein, including without limitation Coleman Cable's standard warranty. Coleman cable disclaims all liability in connection with the use of information contained herein or otherwise.							
This specification is proprietary intellectual property of Coleman Cable. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable.				any party	COLEMAN CABLE, INC		
	* Nbr(s):					tields Drive an, IL 60085	
Approved By:_		_Date:			Phone:	1-800-323-9355	
Title:_		_Company Name:			www.col	emancable.com	