

## F 467K

## GRADE MARK

THREAD DATA		
<b>Size:</b> 3/8	Threads per in.: 16	Series Designation: UNC
Thread Class or Type: 2B	Pitch and Functional Dia.: 0.3401 - 0.3344	Minor Dia Max/Min.: 0.3210 - 0.3070
Tensile Stress Area: 0.0775	<b>Standard:</b> ASME B1.1 - 2003 (R2008)	
DIMENSIONAL DATA		
FILTER - Thread Class or Type: 2B	Type: Hex	<b>Standard:</b> ASME B18.2.2-2015
<b>Size:</b> 3/8	Nominal: 0.375	F - Width Across Flats: 0.562 - 0.551
G - Width Across Corners: 0.650 - 0.628	<b>H - Thickness:</b> 0.337 - 0.320	Runout of Bearing Surface, FIM Proof Stress Up to 150,000 psi: 0.017 Max
Runout of Bearing Surface Proof Stress 150,000 psi and Greater: 0.012 Max		
PHYSICAL REQUIREMENTS		
Nominal: 0.375	Type: Hex	Grade: ASTM F467-2013e2, Silicon Bronze
Typical Material: Cu 651	Hardness: HRB 75 min.	Proof Stress, psi.: 70000
Proof Load, lbs.: 5,425		
FINISH DATA		
Finish: As received steel	K factor (ref. DIN 946): 0.2	
	n.	



