


MERAK COLLECTION MODEL NO. 1501CHM EXECUTIVE HIGH BACK W/CHROME FRAME



CHAIR FUNCTIONS



Pneumatic Seat Height
Adjusts "up and down" seat height relative to the floor.

360 Degree Swivel
Allows seat "Rotation" in a full circle.

Tilt Lock
"Locks seat and back" in an upright position.

Swivel/Tilt Control
Places the "pivot point" directly above the base center and allows the user to lean back in a seated position.

Tilt Tension
Allows user to adjust "resistance" with which chair reclines or tilts.



Gray Leather-Soft Vinyl™ Upholstery



White Leather-Soft Vinyl™ Upholstery

DESCRIPTION

- Clean, contemporary design
- Sturdy, 5-point, 27" chrome base for added stability
- Upholstered in leather-soft vinyl that is sleek & comfortable
- Padded armrests
- Infinite tilt lock mechanism
- Fire-resistant
- Weight Capacity (LBS): 275
- Product Weight (LBS): 46

DIMENSIONS

Overall: 27"W x 29"D x 43¼-46¾"H
Seat: 20¼"W x 21½"D x 20-23"H
Seat to Back Height: 26½"
Floor to Seat: 20-23½"
Cushion Width: 19"
Cushion Depth: 20"
Cushion Fill Material: Foam

CHAIR ARM/BASE

Arm Height (Top to Bottom): 26½-30"
Floor to Arm: 26½-30"
Caster Usage: Dual Wheel

MATERIAL ATTRIBUTES

Leather-Soft Vinyl™
Chrome 5-Point Metal Base
Plastic Casters


SHIPPING DETAILS

Carton Length: 37"
Carton Depth: 18"
Carton Height: 26"
Carton Weight (LBS): 46


UPHOLSTERIES IN STOCK



BLK Black Leather-Soft Vinyl™
(NOR-CAREPLUSBLK)



GRY Gray Leather-Soft Vinyl™
(NOR-CAREPLUSGRY)



WHT White Leather-Soft Vinyl™
(NOR-CAREPLUSWHT)

Last Updated: 01/2020



Warranty: Limited Lifetime

OFFICESOURCE.COM