

## ZODZ.E478898 - Positioning Devices

## Positioning Devices

[See General Information for Positioning Devices](#)**L H DOTTIE CO**6131 GARFIELD AVE  
COMMERCE, CA 90040-3610 USA

E478898

**Nonmetallic Cable Ties - Nylon Investigated to ANSI/UL 62275**

Cat. No.	Type Dsg.	Bundle Diam., mm(in.)		Loop Tensile Str., N(lbf)	Operating Temp., °C(°F)		Min. Install. Temp., °C(°F)	Resistant to UV Light	Plenum Rating	Material Flame Rating	Also Classified to [^] IEC 62275 and EN 62275
		Min	Max		Min	Max					
		<b>DT11</b>	2,21		3 (0.12)	70 (2.76)					
<b>DT11B</b>	2,21	3 (0.12)	70 (2.76)	222 (50)	-40 (-40)	85 (185)	-20 (-4)	Yes	AH-2	V-2	-
<b>DT11BBULK</b>	2,21	3 (0.12)	70 (2.76)	222 (50)	-40 (-40)	85 (185)	-20 (-4)	Yes	AH-2	V-2	-
<b>DT11BULK</b>	2,21	3 (0.12)	70 (2.76)	222 (50)	-40 (-40)	85 (185)	-20 (-4)	-	AH-2	V-2	-
<b>DT14</b>	2,21	3 (0.12)	102 (4.02)	222 (50)	-40 (-40)	85 (185)	-20 (-4)	-	AH-2	V-2	-
<b>DT14B</b>	2,21	3 (0.12)	102 (4.02)	222 (50)	-40 (-40)	85 (185)	-20 (-4)	Yes	AH-2	V-2	-
<b>DT14BULK</b>	2,21	3 (0.12)	102 (4.02)	222 (50)	-40 (-40)	85 (185)	-20 (-4)	-	AH-2	V-2	-
<b>DT14H</b>	2,21	7 (0.28)	102 (4.02)	534 (120)	-40 (-40)	85 (185)	-20 (-4)	-	AH-2	V-2	-
<b>DT14HB</b>	2,21	7 (0.28)	102 (4.02)	534 (120)	-40 (-40)	85 (185)	-20 (-4)	Yes	AH-2	V-2	-
<b>DT21H</b>	2,21	7 (0.28)	140 (5.51)	778 (175)	-40 (-40)	85 (185)	-20 (-4)	-	AH-2	V-2	-
<b>DT21HB</b>	2,21	7 (0.28)	140 (5.51)	778 (175)	-40 (-40)	85 (185)	-20 (-4)	Yes	AH-2	V-2	-
<b>DT36H</b>	2,21	7 (0.28)	263 (10.35)	778 (175)	-40 (-40)	85 (185)	-20 (-4)	-	AH-2	V-2	-
<b>DT36HB</b>	2,21	7 (0.28)	263 (10.35)	778 (175)	-40 (-40)	85 (185)	-20 (-4)	Yes	AH-2	V-2	-
<b>DT4</b>	2,21	1.5 (0.06)	22 (0.87)	80 (18)	-40 (-40)	85 (185)	-20 (-4)	-	AH-2	V-2	-

<b>DT48G</b>	2,21	7 (0.28)	365 (14.37)	778 (175)	-40 (-40)	85 (185)	-20 (-4)	-	AH-2	V-2	-
<b>DT4B</b>	2,21	1.5 (0.06)	22 (0.87)	80 (18)	-40 (-40)	85 (185)	-20 (-4)	Yes	AH-2	V-2	-
<b>DT4BULK</b>	2,21	1.5 (0.06)	22 (0.87)	80 (18)	-40 (-40)	85 (185)	-20 (-4)	-	AH-2	V-2	-
<b>DT5</b>	2,21	1.5 (0.06)	40 (1.57)	80 (18)	-40 (-40)	85 (185)	-20 (-4)	-	AH-2	V-2	-
<b>DT5B</b>	2,21	1.5 (0.06)	40 (1.57)	80 (18)	-40 (-40)	85 (185)	-20 (-4)	Yes	AH-2	V-2	-
<b>DT5BULK</b>	2,21	1.5 (0.06)	40 (1.57)	80 (18)	-40 (-40)	85 (185)	-20 (-4)	-	AH-2	V-2	-
<b>DT6</b>	2,21	3 (0.12)	50 (1.97)	222 (50)	-40 (-40)	85 (185)	-20 (-4)	-	AH-2	V-2	-
<b>DT6B</b>	2,21	3 (0.12)	50 (1.97)	222 (50)	-40 (-40)	85 (185)	-20 (-4)	Yes	AH-2	V-2	-
<b>DT6BBULK</b>	2,21	3 (0.12)	50 (1.97)	222 (50)	-40 (-40)	85 (185)	-20 (-4)	Yes	AH-2	V-2	-
<b>DT6BULK</b>	2,21	3 (0.12)	50 (1.97)	222 (50)	-40 (-40)	85 (185)	-20 (-4)	-	AH-2	V-2	-
<b>DTP11</b>	2,21	3 (0.12)	70 (2.76)	222 (50)	-40 (-40)	85 (185)	-20 (-4)	-	AH-2	V-2	-
<b>DTP14</b>	2,21	3 (0.12)	102 (4.02)	222 (50)	-40 (-40)	85 (185)	-20 (-4)	-	AH-2	V-2	-
<b>DTP6</b>	2,21	3 (0.12)	50 (1.97)	222 (50)	-40 (-40)	85 (185)	-20 (-4)	-	AH-2	V-2	-

Last Updated on 2021-01-12

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2021 UL LLC"