



GRADE MARK

THREAD DATA		
Size: #10	Threads per in.: 32	Series Designation: UNF
Thread Class or Type: 2A	Major Diameter: 0.1891 - 0.1831	Pitch and Functional Dia.: 0.1688 - 0.1658
Tensile Stress Area: 0.0200	<b>Standard:</b> ASME B1.1 - 2003 (R2008)	Length: 3
Length Tolerance: -0.09		
DIMENSIONAL DATA		
Type: 80°/82° - Flat Head - Sltd	<b>Standard:</b> ASME B18.6.3 - 2013	Nominal Diameter: 0.19
A - Head Diameter: 0.362 - 0.333	H - Head Height: 0.116 ref	<b>J - Slot Width:</b> 0.060 - 0.050
T - Slot Depth: 0.053 - 0.034	F - Protrusion Height: 0.042 - 0.025	G - Gage Diameter: 0.313
PHYSICAL REQUIREMENTS		
Nominal: 0.19	Standard: ASME B18.6.3-2013, Machine Screw (carbon steel)	Typical Materials: low carbon steel, 1010 through 1022
Hardness: HRB 100 - 70	Tensile Load, Min. (lbf): 1,200	Yield PSI, 2% Offset, Machined Specimen: 36,000
Tensile Strength, Min. (psi): 60,000	Calculated Shear Load-BODY (ref.)(lbf): 720	Calculated Shear Load-THREADS (ref.)(lbf): 600
Straightness Factor: 0.018	Calculated Pretension <sup>2</sup> (lbf): 540	Tightening Torque <sup>1</sup> : 2 ft.lbf, 23 in.lbf, 2.6 Nm
FINISH DATA		
Finish: Zinc & Clear, non-hexavalent/Cr(VI) free0001"/ 3µm	K factor (ref. DIN 946): 0.22	<b>Standard:</b> ASTM F1941/F1941M-2016, Fe/Zn 3AN

These torque values are based on K factors determined using DIN 946, tightening tension of 75% of the yield strength, and the calculation formula T=KDP. These values are advisory only. The torque for assembling critical joints should be determined and/or verified through actual experimentation by the user. The IFI is not responsible for any losses or claims resulting from the use of these values. Calculated Pretension is equal to 75% of the bolt's yield strength achieved when using the indicated Tightening Torque.



