

## \*SAFETY DATA SHEET\*

### SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

**PRODUCT NAME:** McKesson – Thera Calazinc Body Shield  
**MFR #:** 53-CZ4, 53-CZ4G

**DISTRIBUTED BY:** McKesson Medical-Surgical Inc.  
9954 Mayland Drive, Suite 4000  
Richmond, Virginia 23233

**INFORMATION LINE:** 1-800-777-4908  
Monday – Friday 8:00 a.m. – 6:00 p.m. EST

**EMERGENCY PHONE:** 1-800-424-9300 (CHEMTREC)  
Day or night

**PRODUCT DESCRIPTION:** A viscous pink skin care cream formulated to protect and moisturize the skin.

### 2. HAZARDS IDENTIFICATION

#### Classification

This chemical does not meet the hazardous criteria set forth by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200). However, this Safety Data Sheet (SDS) contains valuable information critical to the safe handling and proper use of this product. This SDS should be retained and available for employees and other users of this product.

**Appearance** Pink cream

**Physical State** Viscous Liquid

**Odor** light floral

### 3. COMPOSITION/INFORMATION ON INGREDIENTS

This product is not hazardous according to OSHA 29 CFR 1910.1200. Components not listed are not hazardous or are below reportable limits.

### 4. FIRST-AID MEASURES

#### First Aid Measures

**GENERAL ADVICE:** Provide this SDS to medical personnel for treatment. Always get medical attention when product is swallowed or when symptoms are significant or persist.

**Eye Contact** Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.

**Skin Contact** If skin irritation develops, wash product off with water.

**Inhalation** NA

**Ingestion** If patient is conscious and alert, dilute by drinking large quantities of water. Allow vomiting to occur if patient is conscious and alert, then call a physician or Poison Control Center.

#### Most important symptoms and effects

**Symptoms** May cause mild eye irritation. May cause gastrointestinal disturbance.

#### Indication of any immediate medical attention and special treatment needed

**Notes to Physician** Treat symptomatically.

## 5. FIRE-FIGHTING MEASURES

### Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Unsuitable Extinguishing Media** Not determined.

### Specific Hazards Arising from the Chemical

Non-flammable.

### Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

## 6. ACCIDENTAL RELEASE MEASURES

### Personal precautions, protective equipment and emergency procedures

**Personal Precautions** Use personal protective equipment as required. Protect from slipping if on floor.

### Methods and material for containment and cleaning up

**Methods for Containment** Throw leaking container in the trash.

**Methods for Clean-Up** Wipe up spill with absorbent cloth or paper towel and dispose in trash. Clean floors thoroughly to prevent slipping.

## 7. HANDLING AND STORAGE

### Precautions for safe handling

**Advice on Safe Handling** Handle in accordance with good industrial hygiene and safety practice.

### Conditions for safe storage, including any incompatibilities

**Storage Conditions** Keep containers tightly closed in a dry, cool and well-ventilated place. Do not contaminate food or feed stuffs. Do not reuse container. Keep out of the reach of children. Store between 40-90°F (4-35°C)

**Incompatible Materials** None known.

## 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

**Exposure Guidelines** No exposure limits noted for ingredient(s) applicable for intended use.

### Appropriate engineering controls

**Engineering Controls** None under normal use conditions.

### Individual protection measures, such as personal protective equipment

**Eye/Face Protection** Avoid contact with eyes.

**Skin and Body Protection** No special technical protective measures are necessary.

**Respiratory Protection** No protective equipment is needed under normal use conditions.

**General Hygiene Considerations** Do not get in eyes. Keep away from food and drink.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

### Information on basic physical and chemical properties

<b>Physical State</b>	Viscous liquid	<b>Odor</b>	Light floral
<b>Appearance</b>	Smooth cream	<b>Odor Threshold</b>	Not determined
<b>Color</b>	Pink		

Property	Values	Remarks • Method
pH	NA	
Melting Point/Freezing Point	Not established	
Boiling Point/Boiling Range	Not determined	
Flash Point	Not flammable	
Evaporation Rate	Not determined	
Flammability (Solid, Gas)	n/a-liquid	
Upper Flammability Limits	Not applicable	
Lower Flammability Limit	Not applicable	
Vapor Pressure	Not established	
Vapor Density	Not established	
Specific Gravity	0.981 - 1.010	
Water Solubility	Insoluble	
Solubility in other solvents	Not determined	
Partition Coefficient	Not determined	
Autoignition Temperature	Not determined	
Decomposition Temperature	Not determined	
Kinematic Viscosity	Not determined	
Dynamic Viscosity	100,000 – 500,000 cps	
Explosive Properties	Not determined	
Oxidizing Properties	Not determined	
Density	8.18 - 8.42 lb/gal	

## 10. STABILITY AND REACTIVITY

### Reactivity

Not reactive under normal conditions.

### Chemical Stability

Stable under recommended storage conditions. Store between 40-90°F (4-35°C)

### Possibility of Hazardous Reactions

None under normal processing.

<b>Hazardous Polymerization</b>	Hazardous polymerization does not occur.
---------------------------------	--

### Conditions to Avoid

None known.

### Incompatible Materials

None known.

### Hazardous Decomposition Products

None known.

## 11. TOXICOLOGICAL INFORMATION

### Information on likely routes of exposure

#### Product Information

<b>Eye Contact</b>	Avoid contact with eyes.
<b>Skin Contact</b>	Not expected to be a skin irritant during prescribed use.
<b>Inhalation</b>	Under normal conditions of intended use, this material is not expected to be an inhalation hazard.
<b>Ingestion</b>	Do not taste or swallow.

### Component Information

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Petrolatum 8009-03-8	> 2000 mg/kg (Rat)	> 2000 mg/kg ( Rabbit )	-

### Information on physical, chemical and toxicological effects

**Symptoms** Please see section 4 of this SDS for symptoms.

### Delayed and immediate effects as well as chronic effects from short and long-term exposure

**Carcinogenicity** This product does not contain any carcinogens or potential carcinogens as listed by OSHA, IARC or NTP.

### Numerical measures of toxicity

Not determined

## 12. ECOLOGICAL INFORMATION

### Ecotoxicity

An environmental hazard cannot be excluded in the event of unprofessional handling or disposal.

Chemical Name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea

### Persistence/Degradability

Not determined

### Bioaccumulation

Not determined

### Mobility

Not determined

### Other Adverse Effects

Not determined

**13. DISPOSAL CONSIDERATIONS**

**Waste Treatment Methods**

- Disposal of Wastes**                      Disposal should be in accordance with applicable regional, national and local laws and regulations.
  
- Contaminated Packaging**                Disposal should be in accordance with applicable regional, national and local laws and regulations.

**14. TRANSPORT INFORMATION**

- Note**    Please see current shipping paper for most up to date shipping information, including exemptions and special circumstances.
  
- DOT**    Not regulated
  
- IATA**    Not regulated
  
- IMDG**    Not regulated

**15. REGULATORY INFORMATION**

**International Inventories**

Not determined

**US Federal Regulations**

**SARA 313**

Not regulated

**US State Regulations**

Not regulated

**U.S. State Right-to-Know Regulations**

Chemical Name	New Jersey	Massachusetts	Pennsylvania
Petrolatum 8009-03-8	-	-	-

**DISCLAIMER:** This information relates onto to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. The information and recommendations contained herein are to the best of the manufacturer's knowledge and belief accurate and reliable as of the date indicated. No representation warranty or guarantee, however, is made with regards to accuracy, reliability or completeness. Conditions of use of the material are under the control of the user; therefore, it is the user's responsibility to satisfy itself as to the suitability and completeness of such information for its own particular use. Appropriate warnings and safe-handling procedures should be provided to handlers and users.