

SAFETY DATA SHEET

SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: Select® PVP Prep Solution

MFR #: 035 and 036

DISTRIBUTED BY: McKesson Medical-Surgical Inc.
9954 Mayland Drive, Suite 4000
Richmond, Virginia 23233

INFORMATION LINE: 1-800-777-4908
Monday – Friday 8:00 a.m. – 6:00 p.m. EST

EMERGENCY PHONE: 1-800-451-8346 (3E Company) Day or Night

PRODUCT DESCRIPTION: Select® PVP Prep Solution

SECTION 2: HAZARDS IDENTIFICATION

ROUTES OF ENTRY: Inhalation, Skin

POTENTIAL HEALTH EFFECTS:

EYES: N/A

SKIN: N/A

INGESTION: N/A

INHALATION: N/A

ACUTE HEALTH HAZARDS: N/A

CHRONIC HEALTH HAZARDS: Prolonged and repeated contact may cause skin irritation.

MEDICAL CONDITIONS GENERALLY AGGRAVATED BY EXPOSURE: N/A

CARCINOGENICITY

OSHA: N/A

ACGIH: N/A

NTP: N/A

IARC: N/A

OTHER: N/A

SECTION 2 NOTES: N/A

SECTION 3: COMPOSITION/INFORMATION OF INGREDIENTS

<u>INGREDIENT</u>	<u>CAS NO.</u>	<u>%</u>	<u>Exposure Limits</u>
-------------------	----------------	----------	------------------------

SECTION 3 NOTES: N/A

SECTION 4: FIRST-AID MEASURES

EYES: In case of contact, flush with water.

SKIN: In case of contact, flush with water.

INGESTION: N/A

INHALATION: If inhaled move to fresh air.

NOTES TO PHYSICIANS OR FIRST AID PROVIDERS: N/A

SECTION 4 NOTES: N/A

SECTION 5: FIRE-FIGHTING MEASURES

FLAMMABLE LIMITS IN AIR, UPPER: N/A
(% BY VOLUME) LOWER: N/A

FLASH POINT: N/A
METHOD USED: N/A

AUTOIGNITION TEMPERATURE: N/A

NFPA HAZARD CLASSIFICATION

HEALTH: N/A **FLAMMABILITY:** N/A **REACTIVITY:** N/A **OTHER:** N/A

HMS HAZARD CLASSIFICATION

HEALTH: N/A **FLAMMABILITY:** N/A **REACTIVITY:** N/A **PERSONAL:** N/A

EXTINGUISHING MEDIA: Water form or foam followed by water.

SPECIAL FIRE FIGHTING PROCEDURES: None.

UNUSUAL FIRE AND EXPLOSION HAZARDS: None.

HAZARDOUS DECOMPOSITION PRODUCTS: None.

SECTION 5 NOTES: N/A

SECTION 6: ACCIDENTAL RELEASE MEASURES

ACCIDENTAL RELEASE MEASURES: Flush with water and clean it thoroughly.

SECTION 6 NOTES: N/A

SECTION 7: HANDLING AND STORAGE

HANDLING: N/A

STORAGE: Store in a cool place.

OTHER PRECAUTIONS: N/A

SECTION 7 NOTES: N/A

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

ENGINEERING CONTROLS:

VENTILATION: Good

RESPIRATORY PROTECTION: None

EYE PROTECTION: Goggles should be used.

SKIN PROTECTION: Gloves to minimize skin contact.

OTHER PROTECTIVE CLOTHING OR EQUIPMENT: None in ordinary use.

WORK HYGIENIC PRACTICES: N/A

EXPOSURE GUIDELINES: N/A

SECTION 8 NOTES: N/A

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE & ODOR:**PHYSICAL STATE:** Redish brown with characteristic iodine odor, free of particulate matter in suspension, or foreign matter.**pH AS SUPPLIED:****pH (Other):** N/A**BOILING POINT:** about 105°C/1atm**MELTING POINT:** N/A**FREEZING POINT:** N/A**VAPOR PRESSURE (mmHg):** negligible

@ N/A

DENSITY (lb/gal): 1.6

@ N/A

SPECIFIC GRAVITY (H₂O = 1): 1.034

@ N/A

EVAPORATION RATE: N/A**BASIS (=1):** N/A**SOLUBILITY IN WATER:****PERCENT SOLIDS BY WEIGHT:** N/A**PERCENT VOLATILE:** N/A**BY WT/ N/A BY VOL @ N/A****VOLATILE ORGANIC COMPOUNDS (VOC):** N/A

WITH WATER:	N/A	LBS/GAL
WITHOUT WATER:	N/A	LBS/GAL

MOLECULAR WEIGHT: N/A**VISCOSITY:** N/A

SECTION 9 NOTES: N/A

SECTION 10: STABILITY AND REACTIVITY

STABLE**UNSTABLE****STABILITY:** X**CONDITIONS TO AVOID (STABILITY):** None observed and none in ordinary use.**INCOMPATIBILITY (MATERIAL TO AVOID):** Strong oxidizing or reducing agents, metal.**HAZARDOUS DECOMPOSITION OR BY-PRODUCTS:** None.**HAZARDOUS POLYMERIZATION:** Will not occur.**CONDITIONS TO AVOID (POLYMERIZATION):** N/A

SECTION 10 NOTES: N/A

SECTION 11: TOXICOLOGICAL INFORMATION

TOXICOLOGICAL INFORMATION:

Toxicity Test:

Acute oral LD50 (mg/kg): 8,800 (rat)

Sensitization: 5,900 patients over 3 year-0.03% incidence of sensitization (humans)

Skin irritation: Non-irritating to rabbit skin (10% aqueous solution); mildly irritating to rabbit skin (as sold)

Eye irritation: Non-irritating to rabbit eye (10% aqueous solution)

SECTION 11 NOTES: N/A

SECTION 12: ECOLOGICAL INFORMATION

ECOLOGICAL INFORMATION:

Biodegradability: Not determined

Aquatic Toxicity: No data available on the adverse effects of this material on the environment.

SECTION 12 NOTES: N/A

SECTION 13: DISPOSAL CONSIDERATIONS

WASTE DISPOSAL METHOD: Dilute it with lots of water and flush down sewer, non-toxic to regulation for pollution.**RCRA HAZARD CLASS:** N/A**SECTION 13 NOTES:** Comply with all federal, state and local regulations.

SECTION 14: TRANSPORT INFORMATION

U.S. DEPARTMENT OF TRANSPORTATION**PROPER SHIPPING NAME:** Not regulated**HAZARD CLASS:** N/A**DOT SHIPPING ID NUMBER:** N/A**DOT PACKING GROUP:** N/A**DOT HAZARD CLASS:** N/A**DOT LABEL STATEMENT:** N/A**WATER TRANSPORTATION****PROPER SHIPPING NAME:** N/A**HAZARD CLASS:** N/A**ID NUMBER:** N/A**PACKING GROUP:** N/A**LABEL STATEMENTS:** N/A**AIR TRANSPORTATION****PROPER SHIPPING NAME:** N/A**HAZARD CLASS:** N/A**ID NUMBER:** N/A**PACKING GROUP:** N/A**LABEL STATEMENTS:** N/A**SECTION 14 NOTES:** N/A

SECTION 15: REGULATORY INFORMATION

U.S. FEDERAL REGULATIONS**TSCA (TOXIC SUBSTANCE CONTROL ACT):** N/A**CERCLA (COMPREHENSIVE RESPONSE COMPENSATION, AND LIABILITY ACT):** N/A**SARA 311/312 HAZARD CATEGORIES:** N/A



SDS DATE: 11/20/15

SARA 313 REPORTABLE INGREDIENTS: Contains NO hazardous ingredients subject to reporting requirements of Section 313 of SARA Title II.

STATE REGULATIONS: N/A

INTERNATIONAL REGULATIONS: N/A

SECTION 15 NOTES: N/A

SECTION 16: OTHER INFORMATION

OTHER INFORMATION: N/A

PREPARATION INFORMATION: N/A

DISCLAIMER: This information relates onto to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. The information and recommendations contained herein are to the best of the manufacturer's knowledge and belief accurate and reliable as of the date indicated. No representation warranty or guarantee, however, is made with regards to accuracy, reliability or completeness. Conditions of use of the material are under the control of the user; therefore, it is the user's responsibility to satisfy itself as to the suitability and completeness of such information for its own particular use. Appropriate warnings and safe-handling procedures should be provided to handlers and users.