
Pan Head - Type I (Phillips)

TYPE I



This type of recess has a large center opening, tapered wings, and blunt bottom, with all edges relieved or rounded.



GRADE MARK

GRADE MARK	
Threads per in.: 32	Series Designation: UNC
Major Diameter: 0.1631 - 0.1571	Pitch and Functional Dia.: 0.1428 - 0.1399
Standard: ASME B1.1 - 2003 (R2008)	Length: 3/8
Standard: ASME B18.6.3 - 2013	Nominal Diameter: 0.164
H - Head Height: 0.115 - 0.105	Driver Size: 2
Wobble: 12°	M - Ref. Recess Dim.: 0.175
Standard: ASME B18.6.3-2013, Machine Screw (Stainless Steel)	Typical Materials: 304 Stainless Steel
Tensile Load, Min. (lbf): 840	Yield PSI, 2% Offset, Machined Specimen: 40,000
Calculated Shear Load-BODY (ref.)(lbf): 504	Calculated Shear Load-THREADS (ref.)(lbf): 420
Calculated Pretension ² (lbf): 420	Tightening Torque ¹ : 1 ft.lbf, 12 in.lbf, 1.4 Nm
K factor (ref. DIN 946): 0.18	
	Major Diameter: 0.1631 - 0.1571 Standard: ASME B1.1 - 2003 (R2008) Standard: ASME B18.6.3 - 2013 H - Head Height: 0.115 - 0.105 Wobble: 12° Standard: ASME B18.6.3-2013, Machine Screw (Stainless Steel) Tensile Load, Min. (lbf): 840 Calculated Shear Load-BODY (ref.)(lbf): 504 Calculated Pretension ² (lbf): 420

¹ These torque values are based on K factors determined using DIN 946, tightening tension of 75% of the yield strength, and the calculation formula T=KDP. These values are advisory only. The torque for assembling critical joints should be determined and/or verified through actual experimentation by the user. The IFI is not responsible for any losses or claims resulting from the use of these values. ² Calculated Pretension is equal to 75% of the bolt's yield strength achieved when using the indicated Tightening Torque.



