

## Hex Washer Head - Unslotted and Sltd - Self-drilling Screw - Type BSD, Style 2 Point Style 2 Point Major Diameter - Major Diameter -





Typical Self-Drilling Tapping Screw Point

THREAD DATA		
Size: #6	Threads per in.: 20	Thread Class or Type: BSD
<b>Major Diameter:</b> 0.1390 - 0.1320	<b>Standard:</b> ASME B18.6.3-2013	
DIMENSIONAL DATA		
Type: Hex Washer Head - Unslotted and Sltd - Self-drilling Screw - Type BSD, Style 2 Point	Standard: IFI - 113	Nominal Diameter: 0.138
H - Head Height: 0.093 - 0.080	<b>J - Slot Width:</b> 0.048 - 0.039	T - Slot Depth: 0.053 - 0.033
F - Protrusion Height: 0.048 Min	G - Gage Diameter: 0.272	<b>A - Hex AF:</b> 0.250 - 0.244
W - Hex AC: 0.272 Min	<b>B - Washer Diameter:</b> 0.328 - 0.302	U - Washer Thickness: 0.025 - 0.015
Z - Min. Point Protrusion: 0.190	L - Minimum Practical Length: 5/16	L - Length: 1/2
Length Tolerance: ± 0.03		
PHYSICAL REQUIREMENTS		
Nominal: 0.138	<b>Standard:</b> IFI - 113/SAE J78 / ASTM C1513	Typical Materials: carbon steel: 1018-1022
Test Plate Thickness in.: 0.060 - 0.064	Torsional Strength, Min. (in.lbf): 24	Core Hardness: HRC 32 - 40
Case Hardness: HRC 52 - 58	Case Depth (in.): .007002	Ductility Test Angle: 5°
Axial Test Load +/- 5% (0.0003 in. max. finish):	Axial Test Load +/- 5% (over 0.0003 in. finish): 35	Max. time to drill & form thread (seconds): 2.5
Test Drill Speed (RPM): 1800 - 2500	Straightness Factor: N/A	
FINISH DATA		
Finish: Zinc & Clear, non-hexavalent/Cr(VI) free0001"/ 3µm	K factor (ref. DIN 946): 0.22	<b>Standard:</b> ASTM F1941/F1941M-2016, Fe/Zn 3AN

<sup>&</sup>lt;sup>1</sup> These torque values are based on K factors determined using DIN 946, tightening tension of 75% of the yield strength, and the calculation formula T=KDP. These values are advisory only. The torque for assembling critical joints should be determined and/or verified through actual experimentation by the user. The IFI is not responsible for any losses or claims resulting from the use of these values. <sup>2</sup> Calculated Pretension is equal to 75% of the bolt's yield strength achieved when using the indicated Tightening Torque.



