

PIG® Heavy-Duty 3-Drum Poly Spill Containment Pallet

PAK213 Holds (3) 55 gal. Poly or Steel Drums, 34.5" x 83" x 8.75", Sump Capacity 66 gal.

The strongest pallets you can buy won't buckle or bow, even under the heaviest loads! Guaranteed for life.

- The strongest, most durable containment pallets you can buy won't buckle or bow. We guarantee it.
- Strong enough for long-term storage of liquids with high specific gravities
- Innovative design transfers weight to load-bearing channels to maximize capacity
- Molded-in sump catches leaks, drips and spills to help you comply with regulations and keep your storage areas clean and safe
- Low height means loading and unloading require less effort and drum tops are within easier reach
- Low-density polyethylene (LDPE) construction resists UV rays, rust, corrosion and most chemicals
- Textured grating adds traction and lifts out for easy sump access
- Optional .75" drain plug lets you empty sump without removing drums or grating
- 2-way forklift entry allows easy movement from either direction (unloaded only)
- Linear design fits perfectly along walls for easy access to each drum
- We test all of our Containment Pallet designs at max load for months to ensure they can handle full capacity at your facility



Item#	Description	Dimensions	Weight
PAK213-WD	With Drain	34.5" W x 83" L x 8.75" H	88 lbs.
PAK213-WOD	Without Drain	34.5" W x 83" L x 8.75" H	88 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
PAK213-WD	With Drain	88cm W x 211cm L x 22cm H	39.9 kg
PAK213-WOD	Without Drain	88cm W x 211cm L x 22cm H	39.9 kg

Specifications

Sump Capacity Range	40 - 69.9 gal.
Dimensions	34.5" W x 83" L x 8.75" H
Recycled Content	43% Post-Industrial Recycled Polyethylene
Load Capacity UDL	4500 lbs.
Sump Capacity	66 gal.
Brand	PIG
Color	Black
Drain	Optional .75" Drain
Double-Stackable Unit	No
Grates	(1) 48" L x 24" W & (1) 24" L x 24" W Grate
Fork Truck Access	Two-Way Fork Access, Move Unloaded Only
Holds	(3) 55 gal. Poly or Steel Drums
Material	Poly
Use With Flammables	No
Sold as	1 each
Weight	88 lbs.
# per Pallet	10
Composition	Polyethylene (LDPE)
UNSPSC	24101905
Pigalog® Page Number	Page 349

Metric Equivalent

Sump Capacity	249.8 L
Load Capacity UDL	2041.2 kg
Weight	39.9 kg
Dimensions	88cm W x 211cm L x 22cm H

Technical Information

Technical Documents

LDPE Products

SPCC: 8 Things You Need to Know

40 CFR 112.7

40 CFR 122.26

40 CFR 264.175

