

PIG® Heavy-Duty 4-Drum Poly Spill Containment Pallet

PAK672 Holds (4) 55 gal. Poly or Steel Drums, 62.5" x 62.5" x 8.75", Sump Capacity 75 gal.

The strongest pallets you can buy won't buckle or bow, even under the heaviest loads! Guaranteed for life.

- The strongest, most durable containment pallets you can buy won't buckle or bow. We guarantee it.
- Strong enough for long-term storage of liquids with high specific gravities
- Innovative design transfers weight to load-bearing channels to maximize capacity
- Molded-in sump catches leaks, drips and spills to help you comply with regulations and keep your storage areas clean and safe
- Low height means loading and unloading require less effort and drum tops are within easier reach
- Low-density polyethylene (LDPE) construction resists UV rays, rust, corrosion and most chemicals
- Textured grating adds traction and lifts out for easy sump access
- Optional .75" drain plug lets you empty sump without removing drums or grating
- 4-way forklift entry allows easy movement from any direction loaded or unloaded (if loaded, drums MUST be properly secured before moving)
- We test all of our Containment Pallet designs at max load for months to ensure they can handle full capacity at your facility



Item#	Description	Dimensions	Weight
PAK672-BK-WD	With Drain	62.5" W x 62.5" L x 8.75" H	137 lbs.
PAK672-BK-WOD	Without Drain	62.5" W x 62.5" L x 8.75" H	137 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
PAK672-BK-WD	With Drain	159cm W x 159cm L x 22cm H	62.1 kg
PAK672-BK-WOD	Without Drain	159cm W x 159cm L x 22cm H	62.1 kg

Specifications

Sump Capacity Range	70 - 99.9 gal.
Dimensions	62.5" W x 62.5" L x 8.75" H
Recycled Content	48% Post-Industrial Recycled Polyethylene
Load Capacity UDL	9000 lbs.
Sump Capacity	75 gal.
Brand	PIG
Drain	Optional .75" Drain
Double-Stackable Unit	No
Grates	(2) 52" L x 26" W Grates
Fork Truck Access	Four-Way Fork Access, Can Move Loaded (Drums MUST be properly secured before moving)
Holds	(4) 55 gal. Poly or Steel Drums
Material	Poly
Use With Flammables	No
Sold as	1 each
Weight	137 lbs.
# per Pallet	10
Composition	Sump: Polyethylene (LDPE) w/ UV Inhibitor Grate: Polyethylene
UNSPSC	24101905
Pigalog® Page Number	Page 349

Metric Equivalent

Sump Capacity	283.9 L
Load Capacity UDL	4082.4 kg
Weight	62.1 kg
Dimensions	159cm W x 159cm L x 22cm H

Technical Information

Technical Documents

LDPE Products

SPCC: 8 Things You Need to Know

40 CFR 112.7

40 CFR 122.26

40 CFR 264.175

