

PIG® Overpack Salvage Drum



PAK709 Storage Capacity 30 gal., UN1H2/X70/S, Thickness .125"

Tough enough for rough handling, guaranteed. Ship your hazardous materials in our UN Rated, FDA-Compliant overpacks to stay compliant with regs.

- Tough UN Rated overpack is built to withstand rough handling. Guaranteed.
- X-rated for Packing Groups I, II and III, so it's ideal for regulated packaging applications, including shipping hazardous materials by land, sea or rail
- Polypropylene material with UV inhibitors is durable, lightweight and chemical-resistant
- Containers are nestable when empty to save storage space
- Designed and proven to withstand the abuse of shipping to help keep hazardous materials safely contained
- Specifically designed and sized for leaking drums up to 16 gallons
- Two broom holes 180-degrees opposite each other on the lid allow 100% positive leverage for easy opening and closing with a broom handle or bar
- Integrated ledges and handles molded into container let you move overpack with a forklift or by hand; foot hold in the drum base allows you to hold the drum securely in position while opening or closing the lid
- Apply a tamperproof seal to alignment holes on lid and drum to ensure contents aren't disturbed
- Features enhanced lid and base design for added strength and security for stacking or if the drum is accidentally dropped
- Made from FDA-Compliant resins for containment of food and cosmetic products

Item#	Description	Dimensions	Weight
PAK709-WH		ext. dia. 23" x 30" H	23 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
PAK709-WH		ext. dia. 58cm x 76cm H	10.4 kg

Specifications

Dimensions	ext. dia. 23" x 30" H
Storage Capacity	30 gal.
Brand	PIG
Bung Type	No Bung Holes
Drum Type	Poly Drum
Interior Dimensions	16.75" Dia. x 27.25" H
Lid Type	Open-Head - Screw-Top
Lining	Unlined
Thickness	.125"
Sold as	1 each
Weight	23 lbs.
New Pig Patent	10,273,038
# per Pallet	8
Composition	Injection Molded Copolymer Polypropylene
UNSPSC	24112109
Pigalog® Page Number	<u>Page 299</u>

Metric Equivalent

Storage Capacity	113.6 L
Weight	10.4 kg
Dimensions	ext. dia. 58cm x 76cm H

Technical Information

Certifications, Approvals and Ratings

Meets FDA requirements, UN1H2/X70/S

Technical Documents

[Instructions for Overpack Containers](#)

49 CFR 173.3(c)(1)



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com