



No. DGMSZ23A12SD016

Experts on International Rules&Regulations for Training, Packing, Storage&Transport of Hazardous Goods

Dangerous Goods Management(China) Ltd.

安全技术说明书

safety data sheet

产品名称: 可充电锂离子电池 ARB-LP 3000
Product name: Rechargeable Li-ion Battery ARB-LP 3000

委托单位: 深圳市朗恒照明技术股份有限公司
Applicant: FENIXLIGHT LIMITED



第一部分 产品及企业标识

Section 1 product and company identification

产品名称: 可充电锂离子电池 ARB-LP 3000

Product name: Rechargeable Polymer Lithium Ion Battery ARB-LP 3000

商标: FENIX

Trademark: FENIX

型号规格: ARB-LP 3000 3.7V 3000mAh 11.1Wh

Model: ARB-LP 3000 3.7V 3000mAh 11.1Wh

生产商: 深圳市华安宏瑞科技有限公司

Manufacturer: Shenzhen HuaGreen Technology Co., Ltd.

企业名称: Company name:	深圳市朗恒照明技术股份有限公司 FENIXLIGHT LIMITED
地址: Address:	深圳市宝安区西乡街道凤凰岗社区水库路 111 星宏科技园 A 栋厂房西侧 2 层、3 层 2F/3F, West of Building A, Xinghong Technology Park, 111 Shuiku Road, Fenghuanggang Community, Xixiang Street, Bao'an District, Shenzhen City, Guangdong Province, China 电话/Tel: 0755-29631163 邮箱/Mail:chengmh@fenixlight.com.cn
邮编: Post code:	518133
邮箱: E-mail:	chengmh@fenixlight.com.cn
传真号码: Fax:	0755-29631183
企业应急电话: Emergency Phone:	0755-29631163

第二部分 危险性概述

Section 2 hazards summarizing

危险性类别: (见第十四部分)

Classification of Danger: (see section 14)

侵入途径: 眼睛、皮肤、食入

Invasion Route: eyes, skin contact, ingestion

健康危害: 正常条件下根据制造商的说明使用锂离子电池不会产生危害。使用不当的情况下,有破裂、火灾、热、内部成分的漏出的风险,并可能造成意外损失。使用不当的行为包括但不限于下列情况:长时间充电、短路,投入火灾,硬物撞击、尖物刺破、破碎、破裂。

Health Hazard: the lithium ion batteries are not hazardous when used according to the instructions of manufacturer under normal conditions. In case of abuse, there's risk of rupture, fire, heat, leakage of internal components, with could cause casualty loss. Abuses include but not limited to the following cases: charged for long time, short circuited, put into fire, whacked with hard object, punctured with acute object, crushed, and broken.

环境危害: 未见报道

Environmental Hazard: Not reported

燃爆危险: 高温或短路条件下可能会引发火灾或爆炸

The Danger of Burning and Exploding: May occur fire or explosion in high temperature or short circuit.

第三部分 成分/组成信息

Section 3 composition/information on ingredients

纯品

混合物

Pure chemical

Mixture

化学组成:

Chemical ingredients:

成分 Chemical ingredient	分子式 Molecular formula	含量(约) % Content (about)	CAS No.
Lithium cobalt oxide	LiCoO ₂	43.5	12190-79-3
Graphite	C	22.7	7782-42-5
Electrolyte	/	17.8	/
Diaphragm	/	0.27	/
Copper foil	Cu	9.08	7440-50-8
Aluminum foil	Al	6.23	7429-90-5
Aluminum Plastic Paper	/	0.05	/
Nickel belt	Ni	0.17	7440-02-0
Aluminum belt	Al	0.17	7429-90-5

第四部分 急救措施

Section 4 first-aid measures

正常环境条件下，眼睛和皮肤接触锂离子电池不会产生危害。在内部有害物质漏出的情况，如果身体部位接触到这些物质，应采取以下措施：

The lithium ion batteries are not hazardous with eye and skin contact under normal circumstance. In case of internal hazardous substance leaking an hazardous substance, following measures should be taken if body parts contact with these substance:

皮肤接触：皮肤接触后马上用肥皂和大量清水冲洗皮肤

After Skin Contact: In case of contact, immediately wash skin with soap and copious amounts of water.

眼睛接触：提起眼皮用清水冲洗 15 分钟，立即就医。

After Eye Contact: In case of contact, flush eyes with clean water for 15 minutes while lifting eyelids. Get prompt medical attention.

吸入：如有吸入，迅速脱离现场至空气新鲜处。如果停止呼吸，进行人工呼吸。如果呼吸困难，供给氧气。

After Inhalation: If inhaled, remove to fresh air. If not breathing give artificial respiration. If breathing is difficult, give oxygen.

食入：如有知觉用水冲洗口腔。就医。

After Ingestion: If swallowed, wash out mouth with water provided person is conscious. Call a physician.

第五部分 消防措施

Section 5 fire-fighting measures

危险特性：在火灾时可释放有害浓烟、气体或者蒸汽。

Characteristics of Hazard: Toxic fumes; gases or vapors may evolve on burning.

有害燃烧产物：一氧化碳和二氧化碳、HF、氟磷化物

Hazardous Combustion Products: CO,CO₂, HF, phosphorus fluoride.

灭火方法及灭火剂：对锂电池，大量冷水是一个有效的灭火剂。不要使用温或热水。不要使用哈龙类灭火材料。可使用干粉、沙、土。

Fire-extinguishing Methods and Extinguishing Media: Copious amounts of cold water are an effective extinguishing medium for lithium batteries. Don't use warm or hot water. Don't use Halon type extinguishing material. May use dry powder, sand, earth.

灭火注意事项：消防人员须佩戴防毒面具、穿全身消防服

Attention in Fire-extinguishing: The Firemen should put on antigas masks and full fire-fighting suits.

第六部分 泄露应急处理

Section 6 accidental release measures

当电池发生泄漏，液体可以用砂，土，或其他惰性物质吸收，受污染的区域应同时通风。

When leakage of batteries happens, liquid could be absorbed with sands, earth, or other inert substance, and the contaminated area should be ventilated meantime.

未放热或燃烧的破损电池，应装入密封的塑料袋或容器。

Damaged batteries that are not hot or burning should be placed in a sealed plastic bag or container.

第七部分 操作处置与储存

Section 7 handling and storage

操作注意事项：不要让接头短路的方式对电池进行操作

Handling: don't handling the batteries in manner that allows terminals to short circuit

储存注意事项：储存和使用时，要远离热、火花、明火或其他点火源热，并处于室温下(<30℃)通风和除湿环境。

Storage: Store and used far away from heat, sparks, open flame, or other heat ignition sources, and under room temperature(<30℃) in ventilating and dehumidifying environments

第八部分 接触控制/个体防护

Section 8 exposure controls/personal protection

最高容许浓度：没有适用标准

Maximum Allowable Concentration: No Standard available

工程控制：操作未破损的电池，没有工程控制要求。对于破损的电池，个人防护用品应包括化学品防护手套和安全眼镜。

Engineering Controls: no engineering controls are required for handling batteries that have not been damaged. Personal protective equipments for damaged batteries should include chemical resistant gloves and safety glasses.

第九部分 理化特性

Section 9 Physical and Chemical Properties

标称电压: 3.7V 额定容量: 3000mAh 额定瓦特小时: 11.1Wh
Nominal Voltage: 3.7V Rated Capacity: 3000mAh Watt-hour rating: 11.1Wh

外观与性状: 黑色长方体

Appearance Characters: Black cuboid

第十部分 稳定性和反应活性

Section 10 stability and reactivity

稳定性: 常温常压下稳定

Stability: Stable under normal temperatures and pressures.

禁配物: 氧化剂

Incompatibility: oxidizing agents

避免接触的条件: 热和明火、短路和水

Conditions to Avoid: Heat and open flame, short circuit, and water

聚合危害: 不会发生

Hazardous polymerization: Will not occur

分解产物: 一氧化碳、二氧化碳、HF、氟磷化物

Decomposition Products: CO,CO₂,HF,phosphorus fluoride

第十一部分 毒理学资料

Section 11 toxicological information

在日常操作和使用中本产品不会引起毒理学性能

This product does not elicit toxicological properties during routine handling and use.

第十二部分 生态学资料

Section 12 ecological information

生态毒性: 无

Ecological Toxicity: N/A

生物降解性: 无

Biodegradability: N/A

非生物降解性: 无

Non-biodegradability: N/A

其它有害作用: 该物质对环境有无明显危害。

Other Hazardous: Will not effect environmental evidently

第十三部分 废弃处置

Section 13 disposal

废弃处置方法: 建议遵照国家和地方法规处置或再利用

Waste Treatment: Recycle or dispose of in accordance with government , state & local regulations.

废弃注意事项: 废电池不能被当作普通垃圾。不能扔进火中或置于高温下。不能解体, 刺穿, 破碎或类似的处理。最好的办法是回收利用。

Attention for Waste Treatment: Deserted batteries couldn't be treated as ordinary trash. Couldn't be thrown into fire or placed in high temperature. Couldn't be dissected, pierced, crushed or treated similarly. Best way is recycling.

第十四部分 运输信息

Section 14 transport information

UN 编号: UN3480, UN3481

UN NO. UN3480, UN3481

运输专有名称: UN3480 Lithium ion batteries
UN3481 Lithium ion batteries contained in equipment
UN3481 Lithium ion batteries packed with equipment

Proper Shipping Name: UN3480 Lithium ion batteries
UN3481 Lithium ion batteries contained in equipment
UN3481 Lithium ion batteries packed with equipment

包装标志: 第 9 类

Labels for Package: Class 9

DGR	《危险品规则》(DGR) 包装说明 PI966 和 PI967 第II部分 Dangerous Goods Regulations (DGR), Packing Instructions PI966 and PI967 Section II	DGR 64 th
IMDG CODE	《国际海运危险货物规则》(IMDG CODE) 特殊规定 188 International Maritime Dangerous Goods Code, Special Provision 188	IMDG CODE (Amdt 40-20)
ADR	《国际危险货物道路运输欧洲协定》(ADR) 特殊规定 188 European Agreement concerning the International Carriage of Dangerous Goods by Road, Special Provision 188	ADR 2023
RID	《国际危险货物铁路运输欧洲协定》(RID) 特殊规定 188 Regulations concerning the International Carriage of Dangerous Goods by Rail, Special Provision 188	RID 2023
当符合上述规定时, 可不被申报为第 9 类危险品运输 May be shipped without being declared as Class 9 dangerous goods, when meet to the requirements above.		

危险品规则规定, 运输前, 每一个电池设计须通过联合国试验和标准手册 38.3 节的测试。

UN38.3 报告编号: DGMSZ20T15LD002.

The dangerous goods regulations require that each battery design must meet the requirements of tests of the UN Manual of Tests and Criteria, Part III, Subsection 38.3, before transport.

UN38.3 Report No: DGMSZ20T15LD002.

第十五部分 法规信息

Section 15 regulatory information

法规信息: 联合国《关于危险货物运输的建议书规章范本》(22 版)、国际航空运输协会《危险品规则》(64 版)、《国际海运危险货物规则》(IMDG CODE) (40-20 版)、《国际危险货物道路运输欧洲协定》(ADR) (2023 版)、《国际危险货物铁路运输欧洲协定》(RID) (2023 版)

Regulatory information: Recommendations on the transport of dangerous goods-model Regulations 22nd, IATA dangerous goods regulations 64th, International Maritime Dangerous Goods Code (40-20), European Agreement concerning the International Carriage of Dangerous Goods by Road (2023), Regulations concerning the International Carriage of Dangerous Goods by Rail (2023)

第十六部分 其他信息

Section16 other information

参考文献：中华人民共和国国家标准（GB/T 16483-2008）化学品安全技术说明书内容和项目顺序、中华人民共和国国家标准（GB/T 17519-2013）化学品安全技术说明书编写指南

Reference: National standard of People's Republic of China.(GB/T 16483-2008) Safety data sheet for chemical products-Content and order of sections, National standard of People's Republic of China. (GB/T 17519-2013) Guidance on the compilation of safety data sheet for chemical products

编制日期：2023年1月12日第一版

MSDS creation date: 2023/01/12 Version: 1.0



上述信息是根据我们目前的知识状况撰写，我们尽力追求其准确性。然而，针对该信息，我们不作任何适销性的承诺，亦不作其他任何明示的或暗示的承诺。我们对该信息的使用不负任何责任，使用者请根据应用需求，自行判断其可用性。

The information above is believed to be accurate and represents the best information currently available to us. However, we make no warranty of merchantability or any other warranty, express or implied, with respect to such information, and we assume no liability resulting from its use. Users should make their own investigations to determine the suitability of the information for their particular purposes. In no way shall the company be liable for any claims, losses, or damages of any third party or for lost profits or any special, indirect, incidental, consequential or exemplary damages, howsoever arising, even if the company has been advised of the possibility of such damages.