

## Double Junction Waterproof pHTestr™ 30

PLS1552 1 each

Replaceable electrodes deliver accurate pH readings, even in harsh conditions.

- Dip in any liquid for accurate readings down to  $\pm 0.01$ ; capable of off-the-chart measurements from -1.00 to +15.00
- Easy-to-read screen displays pH and temperature; adjusts for fluctuating temperatures from 32°F to 122°F to offer greater reliability and consistency
- Unique double-junction electrode withstands plating baths, wastewater, process streams and other harsh liquids
- Intuitive 3-button controls, including one-touch calibration and hold function to freeze readings for later reference
- IP67 rated for protection of electronic equipment enclosures; waterproof, dustproof and will even float



### Specifications

Dimensions	ext. dia. 1.5" x 6.5" L
Battery Type	(4) 1.5V Alkaline Batteries (Included)
Brand	Cole-Parmer Instrument
Sensitivity Limit	$\pm 0.01$ pH Accuracy & a Range of -1.00 to +15.00 pH
Spill Kit Accessory Type	Testing Supplies
Temperature Limit	Works in 32°F to 122°F (0°C to 50°C)
Sold as	1 each
Weight	1 lb.
Composition	Plastic
Includes	1 - pH Tester 1 - Lanyard 1 - Case
Shelf Life	1095 days
UNSPSC	41113301
Pigalog® Page Number	<u>Page 121</u>

### Metric Equivalent

Weight	.5 kg
Dimensions	ext. dia. 3.8cm x 17cm L

### Technical Information

**USOnly**

This product can ONLY be shipped to the United States.



**New Pig**

World's best stuff for leaks, drips and spills.

**One Pork Avenue • Tipton, PA 16684-0304**

1-855-493-4647 • Fax: 1-800-621-7447 • [newpig.com](http://newpig.com) • [hothogs@newpig.com](mailto:hothogs@newpig.com)