

## Guardian Wall-Mount Eye Wash

PLS1619 Wall-Mount; Plumbed, Flow Rate 1.6 gal./Minute



Mount this emergency eyewash station on walls in high-risk areas so workers can flush away contaminants to help prevent serious injuries.

- Wall-mountable eye wash provides easy access to onsite initial treatment (mounting bracket included)
- Chrome-plated brass valve with PTFE seals stays open until manually closed for complete decontamination
- Stainless steel bowl with two spray heads delivers a flood of water for rinsing eyes
- Large push flag makes it easy to activate water flow, even when vision is compromised
- Spray heads include flip-top dust covers plus internal flow control and filter to remove impurities
- Assembled, inspected and water-tested before shipment to ensure quality and reliable performance at your facility



Item#	Description	Dimensions	Weight
PLS1619-OR			6.15 lbs.
PLS1619-SS			6.15 lbs.

### Metric Equivalent:

Item#	Description	Dimensions	Weight
PLS1619-OR			2.8 kg
PLS1619-SS			2.8 kg

### Specifications

Style	Wall-Mount; Plumbed
Brand	Guardian
Capacity	Unlimited
Dispensing Method	Plumbed
Flow Rate	1.6 gal./Minute
Sold as	1 each
Weight	6.15 lbs.

# per Pallet

45

**Composition**

Valve: Chrome Plated Brass  
Bowl: ABS Plastic  
Mounting: Cast Aluminum  
Spray Heads: Polypropylene

**UNSPSC**

46181810

**Pigalog® Page Number**

Page 203

**Metric Equivalent**

**Weight**

2.8 kg

**Technical Information**

**Certifications, Approvals and Ratings**

ANSI Z358.1-2014

**Technical Documents**

Compliance Checklist ANSI / ISEA Z358.1-2014

29 CFR 1910.151(c)



**New Pig**

World's best stuff for leaks, drips and spills.

**One Pork Avenue • Tipton, PA 16684-0304**

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com