

SAFETY DATA SHEET

SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: McKesson – Thera Calazinc Body Shield
MFR #: 53-CZ4, 53-CZ4G

DISTRIBUTED BY: McKesson Medical-Surgical Inc.
9954 Mayland Drive, Suite 4000
Richmond, Virginia 23233

INFORMATION LINE: 1-800-777-4908
Monday – Friday 8:00 a.m. – 6:00 p.m. EST

EMERGENCY PHONE: 1-800-424-9300 (CHEMTREC)
Day or night

PRODUCT DESCRIPTION: A viscous pink skin care cream formulated to protect and moisturize the skin.

2. HAZARDS IDENTIFICATION

Classification

This chemical does not meet the hazardous criteria set forth by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200). However, this Safety Data Sheet (SDS) contains valuable information critical to the safe handling and proper use of this product. This SDS should be retained and available for employees and other users of this product.

Appearance Pink cream

Physical State Viscous Liquid

Odor light floral

3. COMPOSITION/INFORMATION ON INGREDIENTS

This product is not hazardous according to OSHA 29 CFR 1910.1200. Components not listed are not hazardous or are below reportable limits.

4. FIRST-AID MEASURES

First Aid Measures

GENERAL ADVICE: Provide this SDS to medical personnel for treatment. Always get medical attention when product is swallowed or when symptoms are significant or persist.

Eye Contact Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.

Skin Contact If skin irritation develops, wash product off with water.

Inhalation NA

Ingestion If patient is conscious and alert, dilute by drinking large quantities of water. Allow vomiting to occur if patient is conscious and alert, then call a physician or Poison Control Center.

Most important symptoms and effects

Symptoms May cause mild eye irritation. May cause gastrointestinal disturbance.

Indication of any immediate medical attention and special treatment needed

Notes to Physician Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable Extinguishing Media Not determined.

Specific Hazards Arising from the Chemical

Non-flammable.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal Precautions Use personal protective equipment as required. Protect from slipping if on floor.

Methods and material for containment and cleaning up

Methods for Containment Throw leaking container in the trash.

Methods for Clean-Up Wipe up spill with absorbent cloth or paper towel and dispose in trash. Clean floors thoroughly to prevent slipping.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on Safe Handling Handle in accordance with good industrial hygiene and safety practice.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place. Do not contaminate food or feed stuffs. Do not reuse container. Keep out of the reach of children. Store between 40-90°F (4-35°C)

Incompatible Materials None known.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Exposure Guidelines No exposure limits noted for ingredient(s) applicable for intended use.

Appropriate engineering controls

Engineering Controls None under normal use conditions.

Individual protection measures, such as personal protective equipment

Eye/Face Protection Avoid contact with eyes.

Skin and Body Protection No special technical protective measures are necessary.

Respiratory Protection No protective equipment is needed under normal use conditions.

General Hygiene Considerations Do not get in eyes. Keep away from food and drink.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical State	Viscous liquid	Odor	Light floral
Appearance	Smooth cream	Odor Threshold	Not determined
Color	Pink		

Property	Values	Remarks • Method
pH	NA	
Melting Point/Freezing Point	Not established	
Boiling Point/Boiling Range	Not determined	
Flash Point	Not flammable	
Evaporation Rate	Not determined	
Flammability (Solid, Gas)	n/a-liquid	
Upper Flammability Limits	Not applicable	
Lower Flammability Limit	Not applicable	
Vapor Pressure	Not established	
Vapor Density	Not established	
Specific Gravity	0.981 - 1.010	
Water Solubility	Insoluble	
Solubility in other solvents	Not determined	
Partition Coefficient	Not determined	
Autoignition Temperature	Not determined	
Decomposition Temperature	Not determined	
Kinematic Viscosity	Not determined	
Dynamic Viscosity	100,000 – 500,000 cps	
Explosive Properties	Not determined	
Oxidizing Properties	Not determined	
Density	8.18 - 8.42 lb/gal	

10. STABILITY AND REACTIVITY

Reactivity

Not reactive under normal conditions.

Chemical Stability

Stable under recommended storage conditions. Store between 40-90°F (4-35°C)

Possibility of Hazardous Reactions

None under normal processing.

Hazardous Polymerization	Hazardous polymerization does not occur.
---------------------------------	--

Conditions to Avoid

None known.

Incompatible Materials

None known.

Hazardous Decomposition Products

None known.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Eye Contact	Avoid contact with eyes.
Skin Contact	Not expected to be a skin irritant during prescribed use.
Inhalation	Under normal conditions of intended use, this material is not expected to be an inhalation hazard.
Ingestion	Do not taste or swallow.

Component Information

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Petrolatum 8009-03-8	> 2000 mg/kg (Rat)	> 2000 mg/kg (Rabbit)	-

Information on physical, chemical and toxicological effects

Symptoms Please see section 4 of this SDS for symptoms.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Carcinogenicity This product does not contain any carcinogens or potential carcinogens as listed by OSHA, IARC or NTP.

Numerical measures of toxicity

Not determined

12. ECOLOGICAL INFORMATION

Ecotoxicity

An environmental hazard cannot be excluded in the event of unprofessional handling or disposal.

Chemical Name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea

Persistence/Degradability

Not determined

Bioaccumulation

Not determined

Mobility

Not determined

Other Adverse Effects

Not determined

13. DISPOSAL CONSIDERATIONS

Waste Treatment Methods

- Disposal of Wastes** Disposal should be in accordance with applicable regional, national and local laws and regulations.
- Contaminated Packaging** Disposal should be in accordance with applicable regional, national and local laws and regulations.

14. TRANSPORT INFORMATION

- Note** Please see current shipping paper for most up to date shipping information, including exemptions and special circumstances.
- DOT** Not regulated
- IATA** Not regulated
- IMDG** Not regulated

15. REGULATORY INFORMATION

International Inventories

Not determined

US Federal Regulations

SARA 313

Not regulated

US State Regulations

Not regulated

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
Petrolatum 8009-03-8	-	-	-

DISCLAIMER: This information relates onto to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. The information and recommendations contained herein are to the best of the manufacturer's knowledge and belief accurate and reliable as of the date indicated. No representation warranty or guarantee, however, is made with regards to accuracy, reliability or completeness. Conditions of use of the material are under the control of the user; therefore, it is the user's responsibility to satisfy itself as to the suitability and completeness of such information for its own particular use. Appropriate warnings and safe-handling procedures should be provided to handlers and users.