



PIG® Quick Response Roof Leak Diverter Tarp Kit

TLS1120 30" x 30", Leak Diverter Tarp; Hose; Hanging Straps or Magnets; Storage Bag, Install With Hanging Straps or Magnets

Quickly catch and divert overhead leaks before they cause damage with this all-in-one kit featuring a heavy-duty diverter tarp and PIG Absorbent Water Mat Pads. Choose between magnets or adjustable straps for fast and easy hanging.

- Easily keep rain and snow from storming *inside*. Whether condensation and ice, or heavy rain from a high-wind hurricane, this solution will quickly protect your team and what you've built.
- Super-easy installation: choose between magnetic or adjustable hanging straps
- Start with a clean, dry floor: includes 5 wringable, reusable PIG Water Absorbent Mats that absorb nearly a quart of water each for cleaning up any leaks that may have hit the floor
- Multiple hanging points with tear-resistant brass grommets preserve the funnel shape and keep the diverter tarp stable
- Heavy-duty, vinyl-coated leak diverter tarp resists punctures, UV and mildew for a long life – can be reused over and over
- No overflowing, leaking or sagging: pinched corners create a funnel to channel liquids to a drain or collection container
- Easily connect the hose to the diverter tarp with included quick-connect adapter
- Clear, compact drawstring bag is easy to grab for quick response to leaks
- Extra-large drain opening and debris cage prevents clogs from crumbled ceiling tiles, drywall and roofing material
- Includes leak diverter tarp, quick connect adapter, drainage hose, water absorbent mats, carrying bag and either adjustable hanging straps or magnetic hanging clips
- Flow rate of 3.33 gallons per minute when used with a 1/2" ID hose

Item#	Description	Dimensions	Weight
TLS1120-WHS	With Hanging Straps	30" W x 30" L	4.5 lbs.
TLS1120-WMG	With Magnets	30" W x 30" L	4.5 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
TLS1120-WHS	With Hanging Straps	76cm W x 76cm L	2 kg
TLS1120-WMG	With Magnets	76cm W x 76cm L	2 kg

Specifications

Style	Complete Kit
Dimensions	30" W x 30" L
Application	Roofs
Brand	PIG
Contains	Leak Diverter Tarp; Hose; Hanging Straps or Magnets; Storage Bag
Drainage Hose	Included
Color	Translucent
Flow Rate	3.33 gal./Minute
Hanging Straps	Included
Hose Connector	.75" w/ Quick Connect
Installation Method	Hanging Straps or Magnets
Shape	Square
Sold as	1 each
Weight	4.5 lbs.
# per Pallet	60
Composition	Diverter: PVC, Polyester Hose: PVC Straps: Nylon Magnets: Nickel, Neodymium, Stainless Steel
Includes	1 - 30" x 30" Leak Diverter Tarp (TLS552-TR) 4 - 60" Adjustable Hanging Straps Option (TLS559) 1 - .75" Quick Connect Set (TLS680) 4 - 1" Magnetic Hanging Clips Option 1 - 10' L Drainage Hose (TLS690) 1 - 14" x 17" Clear Drawstring Bag 5 - 15" x 19" Water Mat (WTR006)
UNSPSC	24141506
Pigalog® Page Number	Page 247

Metric Equivalent

Weight	2 kg
Dimensions	76cm W x 76cm L

Technical Information

Technical Documents

[Instructions for Assembling PIG® Leak Diverter System](#)



World's best stuff for leaks, drips and spills.

One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com