

VAC-U-MAX® Industrial Wet Vacuum

TLS271 Air Powered, Holds 55 gal.

Wet vac quickly cleans up liquids.

- Must be used with 55-gallon open-head steel drum without clamps for cleaning spills in one step
- VAC-U-MAX Vacuum includes static-conductive PVC 1 1/2" x 15' hose, aluminum wand, floor tool and crevice tool
- Produces a maximum static lift of 215" H2O and 110 SCFM suction
- Input operating range from 37-70 SCFM at 60 psig
- Ideal for cleaning up spills of water or machine oils, removing oil from sumps and other containment, and picking up metal chips and other small debris; use with PIG SpillBlocker Dikes for best results
- Requires a minimum .5" air line for operation
- Not suitable for flammable or corrosive liquids (see TLS417, VAC-U-MAX® Flammable Fuels and Oils Vacuum)



Specifications

Air Flow	100 CFM
Brand	VAC-U-MAX
Capacity	55 gal.
Maximum Suction Power	215" Sealed Pressure
Powered By	Air
Power Requirements	Air: 35 SCFM at 60 PSI (Minimum)
Color	Blue
Spill Kit Accessory Type	Vacuums
Use With Flammables	No
Sold as	1 each
Weight	52.6 lbs.
# per Pallet	6
Composition	Hose: PVC Hand Tool: Aluminum Floor Tool: Plastic Wand: Aluminum
UNSPSC	47121602
Pigalog® Page Number	Page 271

Metric Equivalent

Weight

23.9 kg

Technical Information



New Pig

World's best stuff for leaks, drips and spills.

One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com