

North Silver Shield®/4H® Gloves

WPL262 Thickness 2.7 mil, 16", 1 pair

Lightweight protection from corrosive chemicals.

- Silver Shield gloves resist permeation and breakthrough of even the most dangerous liquids like aromatics, ketones, alcohols, esters and chlorinated and aliphatic solvents
- Also resists water-based solutions of most acids and bases
- Extra-long cuff extends protection past wrist onto forearm
- Ambidextrous and light-weight design is also ideal for underlining other gloves



Item#	Description	Dimensions	Weight
WPL262-M	Medium	16" L	.05 lbs.
WPL262-L	Large	16" L	.05 lbs.
WPL262-XL	X-Large	16" L	.05 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
WPL262-M	Medium	41cm L	23 g
WPL262-L	Large	41cm L	23 g
WPL262-XL	X-Large	41cm L	23 g

Specifications

Style	Chemical-Resistant
Dimensions	16" L
Brand	Honeywell North
Coating	None
Cuff	Flat
Lining	None
Color	Silver
Primary Material	Norfoil®
Thickness	2.7 mil

Texture	None
Sold as	1 pair
Weight	.05 lbs.
Composition	Norfoil® Laminate
UNSPSC	46181504
Pigalog® Page Number	<u>Page 192</u>

Metric Equivalent

Weight	23 g
Dimensions	41cm L

Technical Information

Technical Documents

North Butyl® Gloves

29 CFR 1910.132

29 CFR 1910.138



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com