

# Rugged Ridge™

Track Sliders for Jeep® Seats  
P/N: 13201.03

For: CJ5, CJ7, and Wranglers 1976-1995

## WARNING

This slider kit is designed to be used on the vehicles listed above. Use of this slider kit on any other vehicle or failure to install them correctly may result in an improperly intalled seat. This could result in an unexpected movement of the seat and or the loss of control of vehicle, placing the occupants and others in potential danger.

Before you start installing the seat slider kit, please read all instructions and warnings thoroughly.

This seat slider is to be used with seat belts at ALL TIMES.



Parts list: (1) Left seat slider  
(1) Right seat slider  
(1) Seat adjuster bar  
(2) Inserts (plastic)  
(2) Clips

Tools needed: 13MM Hex Head Socket  
#30 Torque Wrench  
Safety Glasses

**Step 1:** Before you start installation please set parking brake in vehicle and place in gear. Chock wheels to reduce the risk of the vehicle moving.

**Step 2:** Removal of existing seat and slider from Jeep®. Locate the (4) nuts that mount the original slider to seat riser. **DO NOT THROW AWAY THE (4) NUTS.** They will be reused. Nuts are located under the seat riser mounting ledge. After removing the (4) nuts from the seat pull the seat and slider bracket off of seat riser. There will be no reason to remove the seat risers from the vehicle. ( Repeat for other side)

**NOTE: If your original seat track slider is not attached to the riser with nuts, this replacement slider will not work with your original seat riser. Unit will work with Rugged Ridge seat risers. P/N: 13201.01 LH  
13201.02 RH**



**Track Sliders for Jeep® Seats**  
**P/N: 13201.03**

**Step: 3** Remove the original seat sliders from seats if equipped. Press down on track bar adjuster and slide brackets forward to remove rear bolts, slide rearwards for front bolts. After removing bolt, **DO NOT THROW AWAY.. THEY WILL BE REUSED TO RE-INSTALLATION OF NEW SEAT SLIDERS.**

**Step: 4** Install the right slider to seat (Fig.1). Push down on adjuster arm and slide forward to expose the rear mounting hole. Re-install original bolt back into bolt hole and tighten. (fig.2) Push down on adjuster arm and slide rearwards to expose the front mounting hole. Re-install original bolt into bolt hole and tighten. Torque all mounting bolts to 22 ft/lbs using a #30 torx wrench.

(Fig.1)



(Fig.2)



**Step 5:** Insert adjuster arm into right side slider as shown (Fig.3). Install nylon bushing into adjuster arm and press onto slider (Fig.4 & 5). Press cotter pin onto adjuster bar to secure into place (Fig.6).

Fig.3



Fig.4



Fig.5



Fig.6





## Track Sliders for Jeep® Seats

P/N: 13201.03

- Step 6:** Install adjuster arm onto left slider as before (Fig.3, 4, 5, and 6). Do not attach to seat until adjuster arm has been installed.  
After arm has been installed mount the left side slider to the seat (same as step #4). Torque bolts to 22 ft/lbs using a #30 torx wrench.



- Step 7:** Install the seat and slider back in Vehicle.  
Align the studs on the slider with the mounting holes located in the seat riser.  
Re-install the (4) nuts that were removed in step 2. Tighten the nuts to 22ft/lbs using the #30 torx wrench.  
**Additional grease may be added to slotted runners to help with seat adjustment if needed.**



**WARNING** ⚠

Failure to tighten all nuts and bolts to the specified torque can result in the loosening of the seat, and thereby causing serious injury to the occupants and vehicle.



### **LIMITED 90 DAY WARRANTY**

Applies to Rugged Ridge by Omix-ada Inc. Products

Rugged Ridge Off Road (the Company) warrants to the original purchaser of this product that should the product or any part thereof, under normal use and conditions, be proven defective in material or workmanship within 90 DAYS from the date of original purchase, such defect(s) will be repaired or replaced or credited at the Company's sole option.

To obtain repair or replacement within the terms of this Warranty, the product is to be delivered with proof of warranty coverage (e.g. Dated bill of sale), specification of defect(s) to the place of purchase or, with prior approval from the Company (Return Authorization Number is required), freight pre-paid to the Company address listed below.

This warranty does not apply to any product or part thereof which, in the opinion of the Company, has suffered or been damaged through alteration, improper installation, mishandling, misuse, neglect, accident or by acts of nature. THE EXTENT OF THE COMPANY'S LIABILITY UNDER THIS WARRANTY IS LIMITED TO THE REPAIR OR REPLACEMENT PROVIDED ABOVE AND, IN NO EVENT, SHALL THE COMPANY'S LIABILITY EXCEED THE PURCHASE PRICE PAID BY PURCHASER FOR THE PRODUCT.

This Warranty is in lieu of all express warranties or liabilities. ANY IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY, SHALL BE LIMITED TO THE DURATION OF THIS WRITTEN WARRANTY. ANY ACTION FOR BREACH OF ANY WARRANTY HEREUNDER INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY MUST BE BROUGHT WITHIN THE PERIOD OF 90 DAYS FROM DATE OF ORIGINAL PURCHASE.

IN NO CASE SHALL THE COMPANY BE LIABLE FOR ANY CONSEQUENTIAL OR INCIDENTAL DAMAGES FOR BREACH OF THIS OR ANY OTHER WARRANTY, EXPRESS OR IMPLIED, WHATSOEVER. No person or representative is authorized to assume for the Company any liability other than expressed herein in connection with the sale of this product.

Some States do not allow limitations on how long an implied warranty lasts or the exclusion or limitation of incidental or consequential damage, so the above limitations may not apply to you. This warranty gives you specific legal rights and you may also have other rights, which vary from state to state.

Omix-ada Inc.  
460 Horizon Dr. Suite 400  
Suwanee, Georgia 30024

