



**PIG® TuffGrit™ Anti-Slip Runner**

FLM8505 Dry Applications, Base: Vinyl Foam/Top Coat: Aluminum Oxide and Proprietary Sealant, 3' W x 10' L

Durable TuffGrit™ surface on this Anti-Slip Runner provides long-lasting traction in slip zones, transition areas and anywhere you need safe footing.

- Proprietary TuffGrit™ coating is incredibly durable and abrasion resistant; no other grit coating on the market lasts longer
- Exceeds ANSI standards for high slip resistance, far better than tapes or paints; provides extreme traction even in wet areas or applications with light overspray or oily drips (not for use in standing water/oil)
- Engineered to leave no grit behind; safer than other mats that gradually lose their grit -- and their effectiveness -- over time
- Thin profile won't create a trip hazard
- Ideal when transitioning from wet/oily to dry areas, adding traction over uneven surfaces, flat rooftop maintenance applications and more
- Rolls up for easy transport to other parts of your facility; recovers flatness quickly once unrolled
- Available Glow-in-the-Dark border adds visibility in low-light conditions

Item#	Description	Dimensions	Weight
FLM8505-BK		3' W x 10' L x .125" H	20 lbs.
FLM8505-BWY		3' W x 10' L x .125" H	20 lbs.
FLM8505-GBY		3' W x 10' L x .125" H	20 lbs.
FLM8505-YW		3' W x 10' L x .125" H	20 lbs.

**Metric Equivalent:**

Item#	Description	Dimensions	Weight
FLM8505-BK		91cm W x 3m L x 3.2mm H	9.1 kg
FLM8505-BWY		91cm W x 3m L x 3.2mm H	9.1 kg
FLM8505-GBY		91cm W x 3m L x 3.2mm H	9.1 kg
FLM8505-YW		91cm W x 3m L x 3.2mm H	9.1 kg

**Specifications**

<b>Size</b>	3' W x 10' L
<b>Dimensions</b>	3' W x 10' L x .125" H

<b>Chemical Contact</b>	For Light Chemical Splash
<b>Oil/Grease Contact</b>	For Light Oil/Grease Splash
<b>Anti-Slip</b>	Yes
<b>Application</b>	Dry Applications
<b>Beveled Edge</b>	No
<b>Brand</b>	PIG
<b>Drainage Holes</b>	Without Holes
<b>Grit Surface</b>	Yes
<b>Safe for Welding Areas</b>	No
<b>Static-Dissipative</b>	No
<b>Sold as</b>	1 each
<b>Weight</b>	20 lbs.
<b># per Pallet</b>	56
<b>Composition</b>	Base: Vinyl Foam Top Coat: Aluminum Oxide and Proprietary Sealant
<b>UNSPSC</b>	52101510
<b>Pigalog® Page Number</b>	<a href="#">Page 236</a>

## Metric Equivalent

<b>Weight</b>	9.1 kg
<b>Dimensions</b>	91cm W x 3m L x 3.2mm H

## Technical Information

### Technical Documents

[PIG Anti-Fatigue Mat](#)

[Instructions for PIG Anti-Fatigue Matting](#)



**One Pork Avenue • Tipton, PA 16684-0304**

1-855-493-4647 • Fax: 1-800-621-7447 • [newpig.com](http://newpig.com) • [hothogs@newpig.com](mailto:hothogs@newpig.com)