

PIG® 4-Drum Poly Spill Containment Pallet

PAK210 Holds (4) 55 gal. Poly or Steel Drums, 51" x 51" x 10", Sump Capacity 66 gal.

The strongest standard pallet you can buy for everyday drum storage. Tough, affordable containment.



- The strongest standard pallet you can buy for everyday drum storage
- 6,000-lb. UDL capacity is strong enough to support four fully loaded steel or poly drums
- Low 10" height means loading and unloading require less effort and drum tops are within easier reach
- Molded-in sump catches leaks, drips and spills to help you comply with regulations and keep your storage areas clean and safe
- Low-density polyethylene (LDPE) construction resists UV rays, rust, corrosion and most chemicals
- Textured grating adds traction and lifts out for easy sump access
- 2-way forklift entry allows easy movement from either direction (unloaded only)
- Nestable design permits stacking when not in use; lowers cost of bulk shipping
- Compact footprint reduces floor space needed for drum storage
- Optional .75" drain plug lets you empty sump without removing drums or grating
- We test all of our Containment Pallet designs at max load for months to ensure they can handle full capacity at your facility



Item#	Description	Dimensions	Weight
PAK210-WD	With Drain	51" W x 51" L x 10" H	80 lbs.
PAK210-WOD	Without Drain	51" W x 51" L x 10" H	80 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
PAK210-WD	With Drain	130cm W x 130cm L x 25cm H	36.3 kg
PAK210-WOD	Without Drain	130cm W x 130cm L x 25cm H	36.3 kg

Specifications

Sump Capacity Range	40 - 69.9 gal.
Dimensions	51" W x 51" L x 10" H
Recycled Content	40% Post-Industrial Recycled Polyethylene
Load Capacity UDL	6000 lbs.
Sump Capacity	66 gal.
Brand	PIG
Color	Black
Drain	Optional .75" Drain
Double-Stackable Unit	No
Grates	(2) 48" L x 24" W Grates
Fork Truck Access	Two-Way Fork Access, Move Unloaded Only
Holds	(4) 55 gal. Poly or Steel Drums
Material	Poly
Use With Flammables	No
Sold as	1 each
Weight	80 lbs.
# per Pallet	10
Composition	Sump: Polyethylene (LDPE) w/ UV Inhibitor Grate: Polyethylene
UNSPSC	24101905
Pigalog® Page Number	Page 346

Metric Equivalent

Sump Capacity	249.8 L
Load Capacity UDL	2721.6 kg
Weight	36.3 kg
Dimensions	130cm W x 130cm L x 25cm H

Technical Information

Technical Documents

LDPE Products

40 CFR 112.7

40 CFR 122.26

40 CFR 264.175

