




Empowering you to work smarter

PRO
SERIES

NP7DP Vacuum Pump



Performance • Reliability

Dual-Voltage

- Expanded application

Internal Check Valve

- Prevent oil backflow

Dual-Stage Integrated Cylinder Design

- High ultimate vacuum
- High reliability

Forced Oil Circulation

- Improved efficiency and durability

Lifting Hook

- Safe & convenient for roof top use

Model	NP7DP	
Power Supply	V / Hz	115V / 60Hz 230V / 60Hz
Flow Rate	CFM	7
Run Load Amps	A	4A (115V), 1.8A (230V)
Ultimate Vacuum	micron	15
Pump Design		Dual-Stage, AC Motor
Motor Power	HP	3/4
Inlet Port	in	1/4", 3/8", 1/2" Flare
Oil Capacity	oz	15
Dimension	in	14 x 5 x 11.3
Weight	lbs	26

1-YEAR WARRANTY