

PIG® Utility Spill Basin

PAK377 Plastic, 35" x 58" x 12", Sump Capacity 75 gal.



Contain messy cleaning and degreasing jobs with this high-sidewall spill basin.

- 12"-high sidewall creates 75-gallon total capacity
- Open sump for easy access
- 100% polypropylene for superior chemical resistance
- Ideal for containment, parts cleaning and temporary storage of liquids

Specifications

Sump Capacity Range	70 - 99.9 gal.
Style	Standard
Dimensions	35" W x 58" L x 12" H
Sump Capacity	75 gal.
Brand	PIG
Interior Bottom Dimensions	52" L x 29" W
Color	Black
Tray Type	Plastic
Sold as	1 each
Weight	20 lbs.
# per Pallet	30
Composition	High Density Polyethylene (HDPE)
UNSPSC	24111812

Metric Equivalent

Sump Capacity	283.9 L
Weight	9.1 kg
Dimensions	89cm W x 147cm L x 30cm H

Technical Information

Technical Documents

[Tap Trapper® Basin](#)

[40 CFR 112.7](#)

40 CFR 122.26

40 CFR 264.175



New Pig

World's best stuff for leaks, drips and spills.

One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com