

## NRDD Digital DC Recovery Unit



Fastest Twin-Cylinder  
Recovery Unit



Scan to see recovery unit comparison sheet



Digital Backlit Display

Oil-Free Compressor

One Key Operation

Purge Function

Brushless DC Technology

## Fastest in Its Class

### Fastest in Direct Vapor for R410A, R22

- UL verified recovery rate, best performance in its class

### Brushless DC Motor

- Light and more efficient

### Large Backlit Display

- Easy-to-read large LCD display
- Backlit for clarity

### Twin Cylinder with 2-Row Oversized Condenser

- Fast recovery

### Oil-Free Compressor

- Suitable for all commonly used refrigerants

### Purge Function

- Prevent mixing of various refrigerants

Model		NRDD			
Refrigerant Type		Category III: R-12, R-134a, R-401C, R-500 Category IV: R-22, R-401A, R-401B, R-402B, R-407C, R-407D, R-408A, R-409A, R-411A, R-411B, R-412A, R-502, R-509 Category V: R-402A, R-404A, R-407A, R-407B, R-410A, R-507			
Power Supply	V/Hz	115V/60Hz			
Motor	HP	1			
Max Current Draw	A	12			
Compressor		Oil-less, Air-cooled, Piston style			
Automatic Safety Shut-Off		558 psi/38.5 bar			
UL Verified Recovery Rate	lbs/min (kg / min)		R-410A	R-22	R-134a
		Direct Vapor	0.75 (0.34) 🏆	0.64 (0.29) 🏆	0.57 (0.26)
		Direct Liquid	14.44 (6.55)	11.11 (5.04)	7.85 (3.56)
		Push/Pull Liquid	18.41 (8.35)	17.04 (7.73)	12.81 (5.81)
Dimension	in	14.5×9.9×11.7			
Weight	lbs	24.3			

🏆 Industry Fastest



**3-YEAR WARRANTY \***

\* NAVAC offers a 2-year over the counter warranty, but you can extend to 3 years with registration on [navacglobal.com/product-registration](http://navacglobal.com/product-registration) within 30 days of purchase.