



PIG® Poly Storage Shed

PAK754 Holds (8) 55 gal. Poly or Steel Drums, 62.5" x 90" x 93", Sump Capacity 75 gal.

Stack two pallets of four drums each inside this storage shed to free up some floor space at your facility.

- Provides 75 gallons of containment and protected storage for up to eight 55-gallon drums (two stacked pallets)
- Low-density polyethylene (LDPE) construction with UV inhibitors resists UV rays, rust, corrosion and most chemicals
- Molded door vents help reduce fumes and interior condensation
- Removable grates provide easy access to the sump
- Forklift access from all sides makes the empty shed easy to move
- Lockable to help keep contents secure (lock included)



Item#	Description	Dimensions	Weight
PAK754-BWG		62.5" W x 90" D x 93" H	500 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
PAK754-BWG		159cm W x 229cm D x 236cm H	226.8 kg

Specifications

Sump Capacity Range	70 - 99.9 gal.
Dimensions	62.5" W x 90" D x 93" H
Load Capacity UDL	8000 lbs.
Sump Capacity	75 gal.
Access	2 Hinged Doors
Brand	PIG
Drain	None
Fork Truck Access	Two-Way Fork Truck Access
Headroom	42.75"
Holds	(8) 55 gal. Poly or Steel Drums

Interior Dimensions	57" W x 70" D x 78" H
Material	Poly
Use With Flammables	No
Sold as	1 each
Weight	500 lbs.
# per Pallet	1
Composition	Polyethylene
UNSPSC	24101905
Pigalog® Page Number	<u>Page 360</u>

Metric Equivalent

Sump Capacity	283.9 L
Load Capacity UDL	3628.8 kg
Weight	226.8 kg
Dimensions	159cm W x 229cm D x 236cm H

Technical Information

Technical Documents

LDPE Products

40 CFR 112.7

40 CFR 122.26

40 CFR 264.175



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com