

Bradley® Portable Drench Hose & Eye Wash

PLS1617 Portable, Holds 10 gal., Flow Rate 0.4 gal./Minute Minimum

Take this portable eye wash unit anywhere to provide ANSI-compliant emergency flushing.

- Sturdy stainless steel tank withstands industrial work sites; built-in handles make it easy to carry
- Fill unit with potable water and add preservative to keep clean and clear (water-treatment additive sold separately)
- 8' hose extends reach and full-size spray head fully flushes body or equipment
- Twin, chrome-plated brass eye wash heads create gentle cleansing streams when activated by large, highly visible push handle
- Stay-open valve prevents accidental shut off prior to full irrigation
- 10-gallon pressurized tank ensures ANSI standard 15 minutes of 0.4 gpm flow through eye wash or 3 minutes of 3 gpm flow through drench hose
- Tire-filler valve allows convenient pressurizing with standard air compressor or pump
- Attached gauge and relief valve help you monitor and maintain a safe pressure level
- Dust caps protect eye wash and drench hose heads from contamination and automatically release with activation



Bradley

Specifications

| | |
|----------------------|-----------------------------|
| Style | Portable |
| Dimensions | ext. dia. 12.25" x 24.38" H |
| Brand | Bradley |
| Capacity | 10 gal. |
| Dispensing Method | Pressurized |
| Flow Rate | 0.4 gal./Minute Minimum |
| Color | Silver |
| Fluid Storage Method | Tank |
| Sold as | 1 each |
| Weight | 30.09 lbs. |

| | |
|----------------------|-----------------|
| # per Pallet | 12 |
| Composition | Stainless Steel |
| UNSPSC | 46181810 |
| Pigalog® Page Number | <u>Page 205</u> |

Metric Equivalent

| | |
|------------|-------------------------|
| Weight | 13.6 kg |
| Dimensions | ext. dia. 31cm x 62cm H |

Technical Information

Certifications, Approvals and Ratings

ANSI Z358.1-2014

Technical Documents

29 CFR 1910.151(c)



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com