NIO-4RD

4" Iolite Round Deep Adjustable Reflector with 10° Optic

Source: 12W 850lm

PRODUCT DESCRIPTION

4" lolite luminaires can be specified for use with lolite new construction or remodel housings. Die-cast adjustable reflectors optimize visual cut-off and adjustable to aim the light source in desired direction.

- Delivering up to 9038 center beam candlepower (CBCP)
- 2700K, 3000K, 3500K, 4000K @ 90+ CRI
- 10° TIR optic delivers luminous intensity of higher lumen downlights
- · 5-Year limited warranty

SPECIFICATION

Construction: Trims are constructed of heat dissipating, die-cast aluminum. The aluminum die-cast LED heat sink is threaded to fit the trim and transfer heat.

Mounting: Trim includes friction blades to mount securely to housing.

OPTIC

Each luminaire includes 10° TIR optic (Note: cannot be changed in the field) Luminaire is also available with field changeable optics, Click Here for more information.

Lumens / Wattage: 850lm / 12W

Color Temperature: 2700K, 3000K, 3500K, 4000K

Color Rendering Index: 90+CRI

Operating Temperature: Specified by housing

Lifetime: 50,000 hours @ L70 **Dimming:** Specified by housing

COMPATIBLE HOUSINGS

Luminaires are compatible with respective lolite housings manufactured by Nora Lighting.

NHIOICD-48LE4 ICAT New Construction, 120-277V; Triac / ELV / 0-10V ICAT New Construction, 120/277V; Lutron EcoSystem NHIOICD-48LUPEQ NHIOICDCP-48LE4 Chicago Plenum, 120-277V; Triac / ELV / 0-10V NHIOICDCP-48LUPEQ Chicago Plenum, 120/277V; Lutron EcoSystem ICAT Remodel, 120-277V; Triac / ELV / 0-10V NHRIOIC-48LE4

Accessories: Luminaires can accommodate (1) hex louver and (1) translucent deco collar or opaque snoot, no accessory holder is required, see accessories page. Flush mount mud ring is available to give the appearance of trimless, compatible with new construction housings only.

LABELS AND LISTINGS

- cULus Listed for Damp Locations
- **ENERGY STAR certified**
- 5-Year Limited Warranty
- **RoHS Compliant**
- Certified to the high efficacy requirements of California Title 24 JA8-2022




















Type Project Catalog No. Notes

Performance Data			
Part Number	Lumens	CCT	CBCP
NIO-4RD40QWW	874lm	4000K	9038 cd

Delivered lumens will vary depending on CCT and finish

PRODUCT IMAGES & DIMENSIONS



NIN-4RD Round Deep Adjustable Reflector Adjustability:

New Construction: 40° / Remodel: 25°





ΒZ Bronze Reflector



Haze Reflector White Flange



MPW Matte Powder White Reflect



al Metal Reflector Natural Metal Flange

RW

CHMPW

Champagne Haze Reflector

Matte Powder White Flange

MPW	
Matte Powder White Reflector	Natura
Matte Powder White Flange	Natu



White Reflector White Flange

4" Iolite Round Deep Adjustable Reflector with 10° Optic - Dedicated Housing Required Туре Color Temperature

NIO-4RD = Round Deep Adjustable	270 = 2700K	BB = Black / Black
	300 = 3000K	BW = Black / White
	350 = 3500K	BZ = Bronze / Bronze
	400 = 4000K	CHMPW = Champagne / Matte Powder White
		HW = Haze / White
		HZMPW = Haze / Matte Powder White
		MPW = Matte Powder White
		NN = Natural Metal / Natural Metal
		147147 1471 1 (1471 1)

WW = White / White

Compatible Housings

Housing Type

NHIOICD-48LE4 = ICAT New Construction; Triac / ELV / 0-10V NHIOICD-48LUPEQ = ICAT New Construction; Lutron EcoSystem NHIOICDCP-48LE4 = Chicago Plenum; Triac / ELV / 0-10V NHIOICDCP-48LUPEQ = Chicago Plenum; Lutron EcoSystem NHRIOIC-48LE4 = ICAT Remodel; Triac / ELV / 0-10V

Example: NIO-4RD40QWW = 4" lolite Round Deep Adjustable with 10° Optic, 4000K, White finish




4" lolite Accessories

4" Iolite Round Deep Adjustable Reflector with 10° Optic

уре	
roject	
atalog No.	
•	

ACCESSORIES

lolite accessories can be added at any point in the design process. Accessories easily install between LED module and die-cast trim. Luminaire will accommodate (1) hex louver and (1) collar accessory, no accessory holder required.



Die-cast trim







Translucent Decorative Collar

NIO-AS14(color)	5%" length
NIO-AS19(color)	¾" length
NIO-AS26(color)	1" length
Color:	
AM / \ DIII / \ ED //	. I) D / I)

AM (amber), BLU (blue), FR (frosted), R (red) MPW (matte p

Translucent collars color the aperture with the specified color while producing white general light. Collars are available in different lengths. Use to add interest, create a theme, match a theme or define a space.

Opaque Collar Snoot

NIO-AS14(color)	5/8" length
NIO-AS19(color)	¾" length
NIO-AS26(color)	1" length
<u>Color</u> :	
MDW (matta navidar jubita) V	MII (bi+a)

MPW (matte powder white), WH (white)

Opaque snoot greatly reduces aperture brightness while preserving light output.

Hex Cell Louver

NIO-HC	Black

Hex cell louver subtly reduces aperture brightness by reducing light output by about 20%.

FLUSH MOUNT

4" lolite trims can be installed flush with the drywall for a flush mount appearance. A flush mount mud ring is installed after the drywall and a professional drywall finisher floats the ceiling to blend in the mud ring.



Flush Mount Mud Ring

NIO-FMMR-4R Round Mud Ring

Mounts trim flush to ceiling with flange visible. Mud ring attaches to drywall. Only for use with NHIOICD-48 or NHIOICDCP-48 new construction housings and NIO-4R trims. Dimensions: $7-\frac{1}{2}$ " diameter $\frac{1}{2}$ " thick



PHOTOMETRICS


4" Iolite Round Deep Adjustable Reflector with 10° Optic

Type **Project** Catalog No. **Notes**

Test Information

Test Number: NTR1892R1 Part Number: NIO-4RD40QWW Beam Spread: 12° Spot Lumens: 874lm Wattage: 12.42W Efficacy: 70lpw CCT / CRI: 4000K / 90 CRI Spacing Criteria (0°-180°): 0.22

Spacing Criteria (90°-270°): 0.22



	Polar Curve	
		F
2297		70°
4594		50°
6891	++	
9188	10°	30°

Illuminance at a Distance			
Distance from Luminaire	FC at Nadir	Beam Diameter	
6'	251fc	1'-4"	
8'	141fc	1'-8"	
10'	90.4fc	2'-1"	
12'	62.8fc	2'-7"	
14'	46.1fc	3'	

Zonal Lumen Summary

	,		
Zone	Lumens	% Luminaire	
0-30	764	87.3	
0-40	838	95.8	
0-60	863	98.6	
0-90	874	100	
90-180	0	0	
0-180	874	100	

Vertical Angles	Candela		
0	9038		
5	5946		
15	715		
25	316		

76

15

35

45

Candela Table

Lumen Output Multipliers

Color Temperature: 2700K (0.9), 3000K (0.96), 3500K (0.96), 4000K (1.00)

