



Double Door Narcotic Cabinet - #181601

Constructed of durable, heavy duty stainless steel and meet schedule 2 drug storage requirements. They have strong piano hinged doors and a two door, dual locking system to ensure content security. The outside door has a triple bolt wafer lock which opens to a second door secured by a flat key lock with a heavy gauge locking cam. Three extra keys are included for each lock. The ambi top of the cabinet lifts so that the unit can be flipped to accommodate left or right outer door access. Its two aluminum shelves are adjustable and increase storage capacity. Pre-drilled holes that are reinforced with stainless steel mounting discs ensure stable wall attachment. These units are warranted for life & include 1 year on the locks.

- Stainless steel double door cabinet with 2 shelves
- Triple bolt wafer and flat key lock security - 3 keys/lock included
- Ambi top for left/right outer door access
- Pre-drilled holes reinforced with stainless steel mounting discs
- Measures 15”H by 11”W by 4”D
- Unit Has lifetime Warranty (1 Year On Locks)