



WW-VMP / WW-VMR SERIES

VINYL BACKED MASTIC PAD/ROLL

DESCRIPTION	FEATURES
WW-VMP / WW-VMR is an insulating mastic with vinyl backing that provides the superior adhesion and dielectric strength required to seal and insulate electrical connections from buried, submerged or overhead cables up to 1000 volts. The vinyl backing adds mechanical strength and is resistant to UV rays. It is impermeable to ozone, water, soil dirt and corrosive chemicals. WW-VMP / WW-VMR adheres quickly and permanently and will not adversely affect the insulation or the conductive polymer shielding.	<ul style="list-style-type: none"> • Available in roll or pad form • Vinyl backing • UV resistant • High dielectric strength • Superior adhesion to metal, cable insulations and jackets • Excludes moisture, may be direct buried or submerged

MATERIALS	BACKING	ADHESIVE	COLOR	STANDARD SIZES (WIDTH X LENGTH)	PART NUMBER
	Vinyl	Mastic	Black	6.5" x 4" (165mm x 102mm) 4" x 10' (102mm x 3.1m)	WW-VMP-65 WW-VMR-40

TECHNICAL PROPERTIES	CHARACTERISTIC	TYPICAL VALUE	TEST METHOD
	Thickness (mils)	129.13	ASTM D 4325
	Operating temp.: Continuous	194°F, 90°C	ASTM D 4325
	Operating temp.: Emergency overload	266°F, 130°C	ASTM D 4325
	Water absorption (%)	0.10	ASTM D 570
	Copper corrosion (visual)	None	ASTM D 69
	Ozone resistance (visual)	Pass	ASTM D 4325
	UV resistance	Pass	ASTM D 4325
	Dielectric strength (V/mil) ¹	508	ASTM D 149
	Dielectric constant	3.2	ASTM D 150
	Dissipation factor	0.025	ASTM D 150
	Volume resistivity (Ω.cm)	1x10 ¹⁵	ASTM D 257

RECOMMENDED USES	STORAGE	SHELF LIFE
For encapsulating and protecting direct buried low voltage connections and devices, terminations, overhead connectors, duct seals, and cable end seals. Ideal for covering molded joints on CN cables.	In original packaging, placed in horizontal position under cover and temperature between 5°C and 35°C.	60 months from date of manufacture.

¹ 20kV/mm or 500V/mil when tested on a 0,51mm (0,20 in) thick specimen

Data in table represents average test results and are not to be used for specification purpose. The product users should make their own tests to determine the products' suitability for the intended use

LIMITED WARRANTY: NSi Industries LLC warrants that each of its products will be free from material and manufacture defects at the date of shipment (unless specified otherwise). NSi Industries LLC makes or gives no warranty to the distributor, its customers, or the product's end user regarding the product's merchantability and/or suitability for their/its intended use or purpose, and buyer shall assume all risks associated therewith. Provided that the product is proven to be defective, NSi Industries sole obligation and buyer's exclusive remedy shall be through the distributor, at NSi Industries' discretion, to replace, repair, or refund the product proved to be defective within the time period specified above. EXCEPT AS EXPRESSLY SET FORTH HEREIN, NSI INDUSTRIES MAKES OR GIVES NO OTHER WARRANTIES, EXPRESSED OR IMPLIED. Except where prohibited by law, NSi Industries LLC will not be liable for collateral, consequential, indirect or incidental damages arising out of, or connected in any way with the supply of products.