

One-Light Pendant W/HAL AC LED Module

Ceiling cord mounted • Dry location listed



Description:

The simple design of this LED Dome pendant offers complements a wide array of styles from industrial to farmhouse. The 17w LED pendant is 3000K in an Antique Bronze finish with a painted gold interior. This is an ideal fixture for residential and commercial applications.

Specifications:

- Antique Bronze (-20) (painted)
- Aluminum Construction
- Antique Bronze, painted gold inside aluminum shade, White acrylic Diffuser
- LED Module is replaceable (part # 93053641)
- Inspired to enhance modern home decor.
- Complements a wide array of styles from industrial to farmhouse.
- Antique Bronze finish with a painted gold interior.
- Dimmable to 10% with many ELV dimmers
- 1,211 lumens 71.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 10 feet of wire supplied
- ENERGY STAR® qualified

Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1211/71.2 (LM-82)
Lumens/LPW (Delivered)	662/40.4 (LM-79)
CCT	3000 K
CRI	90+
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Dry location listed ENERGY STAR® qualified

P5341-2030K9

Images:



Dimensions:

Diameter: 16"
Height: 8-7/8"
Overall Ht. W/Cord: 129"

Glass
Width: 16"
Length: 16"
Glass 2
Width: 5-13/16"
Length: 5-13/16"
Height: 0-1/2"

Photometrics:

P5341-2030K9

ELECTRICAL DATA	P5341-2030K9
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.142 A
Input Power	17
Power Factor	Greater than 0.90
THD	<20%
FCC	Meets FCC Title 47, Part 15 Class B
Operating Temperature	-30 °C to 30 °C
Dimming	Yes*

*See Dimming Notes for more information

P5341-2030K9


LED Light Engine: 3000 K 90+
 System Wattage: 17
 Fixture delivered lumens: 662
 Fixture Efficacy: 40.4
 Spacing Criteria: 1.2

CANDELA DISTRIBUTION

DEG	CANDELA	LUMENS
0	337	
5	336	32
15	317	89
25	280	129
35	240	150
45	194	148
55	106	93
65	9	16
75	4	4
85	1	1
90	0	

ZONAL LUMEN SUMMARY

ZONE	LUMENS	%FIXT
0-30	250	37.7
0-40	400	60.4
0-60	641	96.7
0-90	662	100.0
90-180	0	0.0
0-180	662	100.0



Test 16.00446 Test Date 02/24/16

P5341-2030K9**Dimming Notes:**

P5341 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron Nova T NTELV-300

Lutron Vienti VTELV-600

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.