## NOBLELIFT

**INDUSTRIAL EQUIPMENT** 





PREMIUM QUICK LIFT PALLET TRUCK

Quick Lift Pallet Truck



## Weight Capacity: 4400 lbs.





## **AUTHORIZED DEALER**



WHY CHOOSE BETWEEN PRICE AND QUALITY WHEN YOU CAN HAVE BOTH

## PREMIUM QUICK LIFT PALLET JACK

- Top class range of pallet trucks with excellent ergonomic designs .
- Professional and ideal storage aid for all variety of manual transport tasks over short distances in stores, warehouses and factory plants.
- Reliable, sturdy, torsion-resistant due to its extremely strong high quality steel profile. German WAGNER paint system ensures best powder coating and painting quality.
- All pivots points are greased for excellent maneuverability and effortless steering. Chromed bearing bushes and joints ensure quiet running application and particularly long service life.
- High quality galvanized whole casting hydraulic pump, robust and durable, with fine control of lowering speed, overload valve, and low maintenance.
- The Noblelift Quick Lift pallet jack can lift the pallet off of the ground with only two pulls of the handle and can reach the maximum raised height with only five.

| Item/Type             |        | ACF44        | Quick lift pallet truck |
|-----------------------|--------|--------------|-------------------------|
| Capacity Q            | Lbs    | 4400         |                         |
| Min. fork height h    | Inches | 2.95         |                         |
| Max. fork height h₁   | Inches | 7.5          |                         |
| Steering wheel        | Inches | Ø 7 x 2      |                         |
| Load roller Single    | Inches | Ø 2.9 x 3.65 |                         |
| Load roller Tandem    | Inches | N/A          |                         |
| Size of fork e*s      | Inches | 6.3 x 2      |                         |
| Width overall forks B | Inches | 27   21      |                         |
| Fork length I         | Inches | 48   42   36 |                         |