

NHRIC-527QAT

5" Shallow IC Air-Tight Line Voltage Remodel Housing

Source: 50W Max. (Varies by trim)

Type

Project

Catalog No.

Notes

PRODUCT DESCRIPTION

Shallow remodel housing for use in existing sheet rock, insulated ceilings can be in direct contact with thermal insulation. Air-tight construction provides energy savings by reducing the flow of air through the ceiling. The housing is labeled for use with Nora 5" line voltage trims and compatible with all LED retrofits.

FEATURES

- Low 5-7/8" profile for existing shallow ceiling plenums
- IC Air-Tight energy saving by reducing the flow of air through the ceiling
- Rated for direct contact with insulation
- cULus listed for damp location and through branch circuit wiring
- Quick connect provided
- Installation-ready for existing sheet rock ceilings

CONSTRUCTION

Housing: 0.040 aluminum housing terminates at 1/4" ceiling flange for even positioning of housing angle within the ceiling. Structural arm consisting of 0.050 structural steel connects housing with junction box. Fixture may be installed in areas where it will have direct contact with thermal insulation.

Air Flow Restriction: Housing has factory installed gaskets to restrict airflow from room into ceiling plenum to <2CFM (cubic feet per minute) in accordance with ASTM-283 Air-Tight requirements.

Socket: Socket is free floating and installs to eyeball, gimbal ring and new trims equipped with socket brackets. Protective cap included to protect socket interior during ceiling painting.

Mounting: Four high tension tempered steel springs secure the housing to an existing sheet rock ceiling. Accommodates ceiling thicknesses from 3/8" to 3/4".

Junction Box: Prewired 15 cubic inch 0.064" thick galvanized steel, with five 1/2", two 3/4" knockouts, four Romex® pryouts, and snap on covers. All leads are #18AWG wire, the ground wire is connected to the bottom, and quick connectors are supplied on all leads. Maximum of 8 no. 12 AWG through branch circuit conductors suitable for at least 90°C permitted in junction box.

Quick Connect Feature: Housing contains three UL approved quick connections that allow insertion of 1/4" stripped solid or tinned standard conductors to be inserted into the connector. Connectors are pre-attached to fixture power, common, and ground circuits.

Thermal Protector: Standard UL thermal protector rated for 90°C is affixed to inner top surface of housing.

ELECTRICAL

Input Voltage: 120V

Socket: Medium base

Lamp: Lamp type based on trim selection



Wattage: 50W max. (wattage varies based on trim selection)

LABELS AND LISTINGS

- cULus Listed for Damp Location w/ Feed Through (Wet Location when used with designated trims)
- Meets or exceeds ASTM-283 Air-Tight Requirements
- Washington State Approved



PRODUCT IMAGES & DIMENSIONS



5" Shallow IC Air-Tight Line Voltage Remodel Housing

Housing Type

NHRIC-527QAT: 5" Shallow IC Air-Tight Line Voltage Remodel Housing

Example: **NHRIC-527QAT** = 5" Shallow IC Air-Tight Line Voltage Remodel Housing