



SAFETY DATA SHEET

Revision date 08-Jan-2019

Version 19

Supersedes Date: 17-Apr-2018

Section 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

Product identifier

Product Code 140.0003457

Product Name AUST TMBR OIL AMBERWOOD

Other means of identification

No information available

Recommended use of the chemical and restrictions on use

Paint, Coatings

Details of the supplier of the safety data sheet

See section 16 for more information

The Valspar Corporation
PO Box 1461
Minneapolis, MN 55440

E-mail address msds@valspar.com

Emergency telephone number

United States of America 1-888-345-5732

Section 2: HAZARDS IDENTIFICATION

Classification

Skin corrosion/irritation	Category 2
Skin sensitization	Category 1
Germ cell mutagenicity	Category 1B
Carcinogenicity	Category 2
Reproductive toxicity	Category 1B
Specific target organ toxicity (single exposure)	Category 3
Aspiration toxicity	Category 1
Flammable liquids	Category 3

Label elements



Signal word

DANGER

HAZARD STATEMENTS

Flammable liquid and vapor
Causes skin irritation
May cause an allergic skin reaction
May cause genetic defects
Suspected of causing cancer
May damage fertility or the unborn child
May cause drowsiness or dizziness
May be fatal if swallowed and enters airways

PREVENTION

Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Wear protective gloves/protective clothing/eye protection/face protection. Wash face, hands and any exposed skin thoroughly after handling. Avoid breathing dust/fume/gas/mist/vapors/spray. Contaminated work clothing should not be allowed out of the workplace. Use only outdoors or in a well-ventilated area. P210 - Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Keep container tightly closed. Ground/bond container and receiving equipment. Use explosion-proof electrical/ ventilating/ lighting/ equipment. Use only non-sparking tools. Take precautionary measures against static discharge.

RESPONSE

IF exposed or concerned: Get medical advice/attention.

Eyes

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.

Skin

If skin irritation or rash occurs: Get medical advice/attention. IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/ shower. Wash contaminated clothing before reuse.

Inhalation

IF INHALED: Remove person to fresh air and keep comfortable for breathing.

Ingestion

IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician. Do NOT induce vomiting.

Fire

In case of fire: Use CO₂, dry chemical, or foam for extinction.

STORAGE

Store locked up. Store in a well-ventilated place. Keep container tightly closed. Store in a well-ventilated place. Keep cool.

DISPOSAL

Dispose of contents/containers in accordance with local regulations.

HAZARDS NOT OTHERWISE CLASSIFIED (HNOC)

No information available.

OTHER HAZARDS

spontaneously combustible material. Risk of self-ignition of used cleaning rags, paper wipes etc. Contaminated materials should be soaked in water and placed in a closed metal container before disposal.

UNKNOWN ACUTE TOXICITY

0% of the mixture consists of ingredient(s) of unknown toxicity.

Section 3: COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No	weight-%
Petroleum distillates, hydrotreated light	64742-47-8	50 - 70
Folpet	133-07-3	0.3 - 1
Carbamic acid, 1H-benzimidazol-2-yl-, methyl ester	10605-21-7	0.1 - 0.3
Zirconium ethyl hexoate	22464-99-9	0.1 - 0.3
2-Butanone, oxime	96-29-7	0.1 - 0.3
Ethylbenzene	100-41-4	0.1 - 0.3

*The exact percentage (concentration) of composition has been withheld as a trade secret.

Section 4: FIRST AID MEASURES

First Aid Measures

General advice

IF exposed or concerned: Get medical advice/attention.

Eye contact

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.

Skin Contact

If skin irritation or rash occurs: Get medical advice/attention. IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/ shower. Wash contaminated clothing before reuse.

Inhalation

IF INHALED: Remove person to fresh air and keep comfortable for breathing.

Ingestion

IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician. Do NOT induce vomiting.

Most important symptoms and effects, both acute and delayed

Symptoms No information available.

Indication of any immediate medical attention and special treatment needed

Note to physicians Treat symptomatically.

Section 5: FIRE FIGHTING MEASURES

Suitable extinguishing media

Dry chemical, CO₂, water spray or alcohol-resistant foam.

Not to be used for safety reasons: Strong water jet

Specific hazards arising from the chemical

Burning produces heavy smoke. Fire may produce irritating and/or toxic gases. In the event of fire and/or explosion do not breathe fumes. May cause sensitization by skin contact. spontaneously combustible material. Risk of self-ignition of used cleaning rags, paper wipes etc. Contaminated materials should be soaked in water and placed in a closed metal container before disposal. Keep product and empty container away from heat and sources of ignition.

Special protective equipment for fire-fighters

Wear self-contained breathing apparatus and protective suit. Cool containers with flooding quantities of water until well after fire is out. Do not allow run-off from fire-fighting to enter drains or water courses.

Section 6: ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions

Avoid breathing vapors or mists. Remove all sources of ignition. Use personal protective equipment as required. Avoid contact with skin, eyes or clothing. Keep people away from and upwind of spill/leak. Evacuate personnel to safe areas. Take precautionary measures against static discharges.

For emergency responders

Use personal protection recommended in Section 8.

Environmental precautions

Do not allow into any sewer, on the ground or into any body of water. If the product contaminates lakes, rivers or sewage, inform appropriate authorities in accordance with local regulations. Prevent further leakage or spillage if safe to do so. Local authorities should be advised if significant spillages cannot be contained.

Methods and material for containment and cleaning up

Methods for containment

Prevent further leakage or spillage if safe to do so.

Methods for cleaning up

Dispose of waste product or used containers according to local regulations. Clean with detergents. Avoid solvent cleaners. Dam up. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Pick up and transfer to properly labeled containers. Clean contaminated surface thoroughly. Take up mechanically, placing in appropriate containers for disposal.

Section 7: HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling

Prevent the creation of flammable or explosive concentrations of vapor in air and avoid vapor concentration higher than the occupational exposure limits. Operators should wear anti-static footwear and clothing and floors should be of the conducting type. Use personal protection recommended in Section 8. Never use pressure to empty container. Comply with the health and safety at work laws. Prevent product from entering drains. Vapors are heavier than air and may spread along floors. Vapors may form explosive mixtures with air. Use only with adequate ventilation. Do not breathe dust/fume/gas/mist/vapors/spray. Use only in well-ventilated areas. Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity). Take precautionary measures against static discharges. Use spark-proof tools and explosion-proof equipment. All equipment used when handling the product must be grounded. Risk of self-ignition of used cleaning rags, paper wipes etc. Contaminated materials should be soaked in water and placed in a closed metal container before disposal.

General Hygiene Considerations

When using do not eat, drink or smoke. Wash contaminated clothing before reuse. Avoid contact with skin, eyes or clothing.

Conditions for safe storage, including any incompatibilities

Storage Conditions

Keep/store only in original container. Store in accordance with local regulations. Keep unauthorized personnel away. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Keep container tightly closed in a dry and well-ventilated place. Keep tightly closed in a dry and cool place.

Incompatible materials

Strong oxidizing agents.

Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Limits

If S* appears in the OEL table, it indicates this chemical contains a skin notation.

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Zirconium ethyl hexoate 22464-99-9	STEL: 10 mg/m ³ Zr TWA: 5 mg/m ³ Zr	TWA: 5 mg/m ³ Zr	IDLH: 25 mg/m ³ Zr TWA: 5 mg/m ³ except Zirconium tetrachloride Zr STEL: 10 mg/m ³ Zr
Ethylbenzene	TWA: 20 ppm	TWA: 100 ppm	IDLH: 800 ppm

100-41-4		TWA: 435 mg/m ³	TWA: 100 ppm TWA: 435 mg/m ³ STEL: 125 ppm STEL: 545 mg/m ³
----------	--	----------------------------	--

Appropriate engineering controls

Engineering Controls

Ensure adequate ventilation, especially in confined areas. Provide local exhaust ventilation. In case of insufficient ventilation, wear suitable respiratory equipment.

Individual protection measures, such as personal protective equipment

Eye/face protection

Tight sealing safety goggles.

Skin and body protection

Wear impervious protective clothing, including boots, gloves, lab coat, apron or coveralls, as appropriate, to prevent skin contact. Wear suitable protective clothing. Personnel should wear anti-static clothing made of natural fiber or of high temperature resistant synthetic fiber.

Hand Protection

There is no one glove material or combination of materials that will give unlimited resistance to any individual or combination of chemicals. Ensure that the breakthrough time of the glove material is not exceeded. Refer to glove supplier for information on breakthrough time for specific gloves. The instructions and information provided by the glove manufacturer on use, storage, maintenance and replacement must be followed. Gloves should be replaced regularly and if there is any sign of damage to the glove material. Always ensure that gloves are free from defects and that they are stored and used correctly. The performance or effectiveness of the glove may be reduced by physical / chemical damage and poor maintenance. Wear protective gloves.

Respiratory protection

When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.

Thermal Protection

No information available

Section 9: PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state	liquid
Appearance	No information available
Odor	Solvent
Color	amber
Odor Threshold	No information available
pH value	No information available
Melting point/freezing point	No information available
Boiling point / boiling range	No information available °C / °F
flash point	40 °C / 104 °F
evaporation rate	No information available
Flammability (solid, gas)	No information available
Flammability Limit in Air	
Upper flammability limit:	No information available
Lower flammability limit:	No information available
Vapor Pressure	No information available
vapor density	No information available
Density (lbs per US gallon)	7.29
specific gravity	No information available
Solubility(ies)	No information available
Partition coefficient	No information available
Autoignition temperature	No information available
Decomposition temperature	No information available
Kinematic viscosity	No information available
Dynamic viscosity	No information available

Other information

Section 10: STABILITY AND REACTIVITY

Reactivity	No information available.
Chemical stability	Stable under normal conditions.
Possibility of Hazardous Reactions	None under normal processing.
Hazardous polymerization	None under normal processing.
Conditions to avoid	Heat, flames and sparks.
Incompatible materials	Strong oxidizing agents.
Hazardous Decomposition Products	Carbon monoxide. Carbon dioxide (CO ₂).

Section 11: TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Eye contact

Not applicable

Skin Contact

May cause an allergic skin reaction

Causes skin irritation

Ingestion

May be fatal if swallowed and enters airways

Inhalation

May cause drowsiness or dizziness

Numerical measures of toxicity - Component Information

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Petroleum distillates, hydrotreated light 64742-47-8	> 5000 mg/kg (Rat)	> 2000 mg/kg (Rabbit)	> 5.2 mg/L (Rat) 4 h
Folpet 133-07-3	= 2636 mg/kg (Rat)	> 22600 mg/kg (Rabbit) > 5000 mg/kg (Rat)	> 5 g/m ³ (Rat) 2 h > 0.48 g/m ³ (Rat) 4 h
Carbamic acid, 1H-benzimidazol-2-yl-, methyl ester 10605-21-7	= 6400 mg/kg (Rat) > 5050 mg/kg (Rat)	= 2 g/kg (Rat) = 8500 mg/kg (Rabbit)	-
Zirconium ethyl hexoate 22464-99-9	-	-	-
2-Butanone, oxime 96-29-7	= 930 mg/kg (Rat)	1000 - 1800 mg/kg (Rabbit)	> 4800 mg/m ³ (Rat) 4 h
Ethylbenzene 100-41-4	= 3500 mg/kg (Rat)	= 15400 mg/kg (Rabbit)	= 17.4 mg/L (Rat) 4 h

Numerical measures of toxicity - Product Information

UNKNOWN ACUTE TOXICITY 0% of the mixture consists of ingredient(s) of unknown toxicity.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Chemical Name	ACGIH	IARC	NTP	OSHA
Ethylbenzene 100-41-4	A3	Group 2B		X

ACGIH (American Conference of Governmental Industrial Hygienists)

A3 - Animal Carcinogen.

IARC (International Agency for Research on Cancer)

Group 2B - Possibly Carcinogenic to Humans.

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present.

Skin corrosion/irritation Causes skin irritation
Serious eye damage/eye irritation Not applicable
Skin sensitization May cause an allergic skin reaction
Respiratory sensitization Not applicable
Germ cell mutagenicity May cause genetic defects
Carcinogenicity Suspected of causing cancer
Reproductive Toxicity May damage fertility or the unborn child
Specific target organ toxicity (single exposure) May cause drowsiness or dizziness
Specific target organ toxicity (repeated exposure) Not applicable
Aspiration hazard May be fatal if swallowed and enters airways

Section 12: ECOLOGICAL INFORMATION

Ecotoxicity

Environmental precautions Prevent product from entering drains.

Marine pollutant This material meets the definition of a marine pollutant

Persistence and degradability

No information available

Bioaccumulation

No information available

Mobility

No information available

Other adverse effects

No information available

Section 13: DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal of wastes Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging Improper disposal or reuse of this container may be dangerous and illegal. Empty containers must be scrapped or reconditioned.

Section 14: TRANSPORT INFORMATION

14.1 UN/ID no	DOT UN1263	IMDG UN1263	IATA UN1263
14.2 Proper shipping name	Paint	Paint	Paint
14.3 Hazard Class	COMBUSTIBLE LIQUID	3	3
14.4 Packing Group	III	III	III
14.5 Environmental hazard			
Marine pollutant	This material meets the definition of a marine pollutant		
Marine pollutant	Petroleum distillates, hydrotreated light , Folpet		
14.6 Special Provisions	B1, B52, IB3, T2, TP1, TP29, 367	163, 223, 367 955	A3, A72, A192
	Emergency Response Guide Number 128	EmS-No F-E, S-E	
14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code			No information available

The supplier may apply one of the following exceptions: Combustible Liquid (49 CFR 173.150(f)); Consumer Commodity (49 CFR 173.150(c), ICAO/IATA SP A112); Limited Quantity (49 CFR 173.150(b), ICAO Part 3 Chapter 4, IATA 2.7, IMDG Chapter 3.4); Viscous Liquid (49 CFR 173.121(b), IMDG 2.3.2.2, IATA 3.3.3.1.1, ICAO 3.2.2, ADR 2.2.3.1.5); Does Not Sustain Combustion (49 CFR 173.120(a), IATA 3.3.1.3, ICAO 3.1.3, IMDG 2.3.1.3, ADR 2.2.3.1.1 Note 1); or others as allowed under hazardous materials/dangerous goods regulations.

Section 15: REGULATORY INFORMATION

International Inventories

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

All components are listed or exempt from listing.

DSL - Canadian Domestic Substances List

Not all components are listed or exempt from listing

US Federal Regulations

Chemical Name	SARA 313 - Threshold Values %	Metals	Hazardous air pollutants (HAPs) content
Ethylbenzene 100-41-4 0.1 - 0.3	0.1		Present

Chemical Name	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Ethylbenzene 100-41-4	1000 lb	X	X	X

Chemical Name	Hazardous Substances RQs	CERCLA/SARA RQ	Reportable Quantity (RQ)
Carbamic acid, 1H-benzimidazol-2-yl-, methyl ester 10605-21-7	10 lb		RQ 10 lb final RQ RQ 4.54 kg final RQ
Ethylbenzene 100-41-4	1000 lb		RQ 1000 lb final RQ RQ 454 kg final RQ

US State Regulations

Rule 66 status of product

Not photochemically reactive.

California Proposition 65

WARNING: This product contains chemicals known to the State of California to cause cancer.

U.S. EPA Label information

EPA Pesticide registration number Not applicable

U.S. State Right-to-Know Regulations

Chemical Name
Petroleum distillates, hydrotreated light 64742-47-8
Proprietary Non-Hazardous Ingredient - Proprietary CAS
Proprietary Non-Hazardous Ingredient - Proprietary CAS
Paraffin waxes and Hydrocarbon waxes 8002-74-2
Folpet 133-07-3
Carbamic acid, 1H-benzimidazol-2-yl-, methyl ester 10605-21-7
Zirconium ethyl hexoate 22464-99-9
2-Butanone, oxime 96-29-7
Ethylbenzene 100-41-4

Section 16: OTHER INFORMATION

HMIS

Health hazards	3*
* = Chronic Health Hazard	
Flammability	2
Physical hazards	0
Personal Protection	X

Supplier Address

Valspar Consumer Headquarters 8725 W. Higgins Rd. Suite 1000 Chicago, IL 60631 773-628-5500	The Valspar Corporation 4999 36th St. Grand Rapids, MI 49512 800-253-3957	Valspar Plasti-Kote 1636 Shawson Dr. Mississauga, Ontario L4W 1N7 905-671-8333
--	--	---

Prepared By Product Stewardship

Revision date 08-Jan-2019
Revision Note No information available

Disclaimer

The information on this Safety Data Sheet (SDS) is based on the present state of our knowledge, current national legislation and guidelines. As the specific conditions of use of the product are outside the supplier's knowledge and control the user is responsible for ensuring that the requirements of relevant legislation are complied with. This SDS should not be construed as any guarantee of the technical performance or suitability for particular applications. **UNLESS SUPPLIER AGREES OTHERWISE IN WRITING, SUPPLIER MAKES NO WARRANTIES, EXPRESS OR IMPLIED, AND DISCLAIMS ALL IMPLIED WARRANTIES INCLUDING WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR USE OR FREEDOM FROM PATENT INFRINGEMENT. SUPPLIER WILL NOT BE LIABLE FOR ANY SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES.**

End of Safety Data Sheet