



# SAFETY DATA SHEET

Revision date 02-Mar-2018

Version 16

Supersedes Date: 20-Oct-2017

## Section 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

### Product identifier

**Product Code** 140.0010241

**Product Name** CABT WB BLCHNG ST

### Other means of identification

No information available

### Recommended use of the chemical and restrictions on use

Paint, Coatings

### Details of the supplier of the safety data sheet

*See section 16 for more information*

The Valspar Corporation  
PO Box 1461  
Minneapolis, MN 55440

**E-mail address** [msds@valspar.com](mailto:msds@valspar.com)

### Emergency telephone number

United States of America 1-888-345-5732

## Section 2: HAZARDS IDENTIFICATION

### Classification

Skin sensitization	Category 1
Germ cell mutagenicity	Category 1B
Carcinogenicity	Category 1A
Reproductive toxicity	Category 1B

### Label elements



Signal word

**DANGER**

#### HAZARD STATEMENTS

May cause an allergic skin reaction  
May cause genetic defects  
May cause cancer  
May damage fertility or the unborn child

#### PREVENTION

Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Wear protective gloves/protective clothing/eye protection/face protection. Avoid breathing dust/fume/gas/mist/vapors/spray. Contaminated work clothing should not be allowed out of the workplace.

#### RESPONSE

IF exposed or concerned: Get medical advice/attention.

##### Eyes

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.

##### Skin

IF ON SKIN: Wash with plenty of soap and water. If skin irritation or rash occurs: Get medical advice/attention. Wash contaminated clothing before reuse.

##### Inhalation

IF INHALED: Call a POISON CENTER or doctor if you feel unwell.

##### Ingestion

Do NOT induce vomiting. IF SWALLOWED: Call a POISON CENTER or doctor/physician if you feel unwell.

#### STORAGE

Store locked up.

#### DISPOSAL

Dispose of contents/containers in accordance with local regulations.

#### HAZARDS NOT OTHERWISE CLASSIFIED (HNOC)

No information available.

#### OTHER HAZARDS

Not applicable.

#### UNKNOWN ACUTE TOXICITY

0% of the mixture consists of ingredient(s) of unknown toxicity.

### Section 3: COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No	weight-%
Titanium dioxide	13463-67-7	1 - 3
Chlorothalonil	1897-45-6	0.3 - 1
Carbamic acid, 1H-benzimidazol-2-yl-, methyl ester	10605-21-7	0.1 - 0.3
Quartz	14808-60-7	0.1 - 0.3
Diuron	330-54-1	0.1 - 0.3

\*The exact percentage (concentration) of composition has been withheld as a trade secret.

## Section 4: FIRST AID MEASURES

### First Aid Measures

#### **General advice**

IF exposed or concerned: Get medical advice/attention.

#### **Eye contact**

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.

#### **Skin Contact**

IF ON SKIN: Wash with plenty of soap and water. If skin irritation or rash occurs: Get medical advice/attention. Wash contaminated clothing before reuse.

#### **Inhalation**

IF INHALED: Call a POISON CENTER or doctor if you feel unwell.

#### **Ingestion**

Do NOT induce vomiting. IF SWALLOWED: Call a POISON CENTER or doctor/physician if you feel unwell.

### Most important symptoms and effects, both acute and delayed

**Symptoms** No information available.

### Indication of any immediate medical attention and special treatment needed

**Note to physicians** Treat symptomatically.

## Section 5: FIRE FIGHTING MEASURES

### Suitable extinguishing media

Dry chemical, CO<sub>2</sub>, water spray or alcohol-resistant foam.

Not to be used for safety reasons: Strong water jet

### Specific hazards arising from the chemical

Burning produces heavy smoke. Fire may produce irritating and/or toxic gases. In the event of fire and/or explosion do not breathe fumes. May cause sensitization by skin contact.

### Special protective equipment for fire-fighters

Wear self-contained breathing apparatus and protective suit. Cool containers with flooding quantities of water until well after fire is out. Do not allow run-off from fire-fighting to enter drains or water courses.

## Section 6: ACCIDENTAL RELEASE MEASURES

### Personal precautions, protective equipment and emergency procedures

#### **Personal precautions**

Avoid breathing vapors or mists. Remove all sources of ignition. Use personal protective equipment as required. Avoid contact with skin, eyes or clothing. Keep people away from and upwind of spill/leak.

#### **For emergency responders**

Use personal protection recommended in Section 8.

### Environmental precautions

Do not allow into any sewer, on the ground or into any body of water. If the product contaminates lakes, rivers or sewage, inform appropriate authorities in accordance with local regulations. Prevent further leakage or spillage if safe to do so. Local authorities should be advised if significant spillages cannot be contained.

### Methods and material for containment and cleaning up

### Methods for containment

Prevent further leakage or spillage if safe to do so.

### Methods for cleaning up

Dispose of waste product or used containers according to local regulations. Clean with detergents. Avoid solvent cleaners. Dam up. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Pick up and transfer to properly labeled containers. Clean contaminated surface thoroughly. Take up mechanically, placing in appropriate containers for disposal.

## Section 7: HANDLING AND STORAGE

### Precautions for safe handling

#### Advice on safe handling

Prevent the creation of flammable or explosive concentrations of vapor in air and avoid vapor concentration higher than the occupational exposure limits. Use personal protection recommended in Section 8. Never use pressure to empty container. Comply with the health and safety at work laws. Prevent product from entering drains. Vapors are heavier than air and may spread along floors. Vapors may form explosive mixtures with air. Use only with adequate ventilation. Do not breathe dust/fume/gas/mist/vapors/spray.

#### General Hygiene Considerations

When using do not eat, drink or smoke. Wash contaminated clothing before reuse. Avoid contact with skin, eyes or clothing.

### Conditions for safe storage, including any incompatibilities

#### Storage Conditions

Keep/store only in original container. Store in accordance with local regulations. Keep unauthorized personnel away. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Keep container tightly closed in a dry and well-ventilated place.

#### Incompatible materials

Strong oxidizing agents.

## Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

### Control parameters

#### Exposure Limits

If S\* appears in the OEL table, it indicates this chemical contains a skin notation.

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Titanium dioxide 13463-67-7	TWA: 10 mg/m <sup>3</sup>	TWA: 15 mg/m <sup>3</sup> total dust	IDLH: 5000 mg/m <sup>3</sup>
Quartz 14808-60-7	TWA: 0.025 mg/m <sup>3</sup> respirable particulate matter	TWA: 50 µg/m <sup>3</sup> TWA: (250)/(%SiO <sub>2</sub> + 5) mppcf TWA respirable fraction TWA: (10)/(%SiO <sub>2</sub> + 2) mg/m <sup>3</sup> TWA respirable fraction	IDLH: 50 mg/m <sup>3</sup> respirable dust TWA: 0.05 mg/m <sup>3</sup> respirable dust
Diuron 330-54-1	TWA: 10 mg/m <sup>3</sup>		TWA: 10 mg/m <sup>3</sup>

### Appropriate engineering controls

#### Engineering Controls

Ensure adequate ventilation, especially in confined areas. Provide local exhaust ventilation. In case of insufficient ventilation, wear suitable respiratory equipment.

### Individual protection measures, such as personal protective equipment

#### Eye/face protection

Tight sealing safety goggles.

#### Skin and body protection

Wear impervious protective clothing, including boots, gloves, lab coat, apron or coveralls, as appropriate, to prevent skin contact. Wear suitable protective clothing.

**Hand Protection**

There is no one glove material or combination of materials that will give unlimited resistance to any individual or combination of chemicals. Ensure that the breakthrough time of the glove material is not exceeded. Refer to glove supplier for information on breakthrough time for specific gloves. The instructions and information provided by the glove manufacturer on use, storage, maintenance and replacement must be followed. Gloves should be replaced regularly and if there is any sign of damage to the glove material. Always ensure that gloves are free from defects and that they are stored and used correctly. The performance or effectiveness of the glove may be reduced by physical / chemical damage and poor maintenance. Wear protective gloves.

**Respiratory protection**

When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.

**Thermal Protection**

No information available

## Section 9: PHYSICAL AND CHEMICAL PROPERTIES

**Information on basic physical and chemical properties**

<b>Physical state</b>	liquid
<b>Appearance</b>	No information available
<b>Odor</b>	Slight
<b>Color</b>	Silver
<b>Odor Threshold</b>	No information available
<b>pH value</b>	No information available
<b>Melting point/freezing point</b>	No information available
<b>Boiling point / boiling range</b>	No information available °C / °F
<b>flash point</b>	96 °C / 205 °F
<b>evaporation rate</b>	No information available
<b>Flammability (solid, gas)</b>	No information available
<b>Flammability Limit in Air</b>	
<b>Upper flammability limit:</b>	No information available
<b>Lower flammability limit:</b>	No information available
<b>Vapor Pressure</b>	No information available
<b>vapor density</b>	No information available
<b>Density (lbs per US gallon)</b>	9.72
<b>specific gravity</b>	1.16
<b>Solubility(ies)</b>	No information available
<b>Partition coefficient</b>	No information available
<b>Autoignition temperature</b>	No information available
<b>Decomposition temperature</b>	No information available
<b>Kinematic viscosity</b>	No information available
<b>Dynamic viscosity</b>	No information available

**Other information**

## Section 10: STABILITY AND REACTIVITY

<b>Reactivity</b>	No information available.
<b>Chemical stability</b>	Stable under normal conditions.
<b>Possibility of Hazardous Reactions</b>	None under normal processing.
<b>Hazardous polymerization</b>	None under normal processing.
<b>Conditions to avoid</b>	Heat, flames and sparks.
<b>Incompatible materials</b>	Strong oxidizing agents.
<b>Hazardous Decomposition Products</b>	Carbon monoxide. Carbon dioxide (CO2).

## Section 11: TOXICOLOGICAL INFORMATION

### Information on likely routes of exposure

**Eye contact**

Not applicable

**Skin Contact**

May cause an allergic skin reaction

**Ingestion**

Not applicable

**Inhalation**

Not applicable

### Numerical measures of toxicity - Component Information

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Titanium dioxide 13463-67-7	> 10000 mg/kg ( Rat )	-	-
Chlorothalonil 1897-45-6	= 10 g/kg ( Rat ) > 10000 mg/kg ( Rat )	> 2500 mg/kg ( Rat ) > 10 g/kg ( Rabbit )	= 0.31 mg/L ( Rat ) 1 h = 0.1 mg/L ( Rat ) 4 h
Carbamic acid, 1H-benzimidazol-2-yl-, methyl ester 10605-21-7	= 6400 mg/kg ( Rat ) > 5050 mg/kg ( Rat )	= 2 g/kg ( Rat ) = 8500 mg/kg ( Rabbit )	-
Quartz 14808-60-7	= 500 mg/kg ( Rat )	-	-
Diuron 330-54-1	= 1017 mg/kg ( Rat ) = 4990 mg/kg ( Rat )	> 5 g/kg ( Rat ) > 2000 mg/kg ( Rat )	> 0.265 mg/L ( Rat )

### Numerical measures of toxicity - Product Information

The following values are calculated based on chapter 3.1 of the GHS document .

ATEmix (inhalation-dust/mist) 11.5 mg/l

**UNKNOWN ACUTE TOXICITY** 0% of the mixture consists of ingredient(s) of unknown toxicity.

### Delayed and immediate effects as well as chronic effects from short and long-term exposure

**Carcinogenicity**

According to IARC, Volume 93, no significant exposure to primary particles of titanium dioxide is thought to occur from use in paints since the pigment is bound to other materials.

Chemical Name	ACGIH	IARC	NTP	OSHA
Titanium dioxide 13463-67-7		Group 2B		X
Chlorothalonil 1897-45-6		Group 2B		X
Quartz 14808-60-7	A2	Group 1	Known	X

ACGIH (American Conference of Governmental Industrial Hygienists)

A2 - Suspected Human Carcinogen.

IARC (International Agency for Research on Cancer)

Group 1 - Carcinogenic to Humans. Group 2B - Possibly Carcinogenic to Humans.

NTP (National Toxicology Program)

Known - Known Carcinogen.

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present.

**Skin corrosion/irritation** Not applicable

**Serious eye damage/eye irritation** Not applicable

**Skin sensitization** May cause an allergic skin reaction

**Respiratory sensitization** Not applicable

**Germ cell mutagenicity** May cause genetic defects

**Carcinogenicity** May cause cancer

**Reproductive Toxicity** May damage fertility or the unborn child

**Specific target organ toxicity (single exposure)** Not applicable

**Specific target organ toxicity (repeated exposure)** Not applicable

**Aspiration hazard** Not applicable

## Section 12: ECOLOGICAL INFORMATION

### Ecotoxicity

Environmental precautions Prevent product from entering drains.

Marine pollutant This material meets the definition of a marine pollutant

### Persistence and degradability

No information available

### Bioaccumulation

No information available

### Mobility

No information available

### Other adverse effects

No information available

## Section 13: DISPOSAL CONSIDERATIONS

### Waste treatment methods

**Disposal of wastes** Disposal should be in accordance with applicable regional, national and local laws and regulations.

**Contaminated packaging** Improper disposal or reuse of this container may be dangerous and illegal. Empty containers must be scrapped or reconditioned.

## Section 14: TRANSPORT INFORMATION

	<u>DOT</u>	<u>IMDG</u>	<u>IATA</u>
14.1 UN/ID no	UN3082	UN3082	UN3082
14.2 Proper shipping name	Environmentally hazardous substance, liquid, n.o.s. Chlorothalonil Carbamic acid, 1H-benzimidazol-2-yl-, methyl ester	Environmentally hazardous substance, liquid, n.o.s. Chlorothalonil Carbamic acid, 1H-benzimidazol-2-yl-, methyl ester	Environmentally hazardous substance, liquid, n.o.s.
14.3 Hazard Class	9	9	9
14.4 Packing Group	III	III	III
14.5 Environmental hazard			
<b>Marine pollutant</b>	This material meets the definition of a marine pollutant		
<b>Marine pollutant</b>	Chlorothalonil , Carbamic acid, 1H-benzimidazol-2-yl-, methyl ester		
14.6 Special Provisions	8, 146, 173, 335, IB3, T4, TP1, TP29	274, 335, 969 <b>EmS-No</b> F-A, S-F	A97, A158, A197
14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	<b>Emergency Response Guide Number</b> 171		No information available

*The supplier may apply one of the following exceptions: Combustible Liquid (49 CFR 173.150(f)); Consumer Commodity (49 CFR 173.150(c), ICAO/IATA SP A112); Limited Quantity (49 CFR 173.150(b), ICAO Part 3 Chapter 4, IATA 2.7, IMDG Chapter 3.4); Viscous Liquid (49 CFR 173.121(b), IMDG 2.3.2.2, IATA 3.3.3.1.1, ICAO 3.2.2, ADR 2.2.3.1.5); Does Not Sustain Combustion (49 CFR 173.120(a), IATA 3.3.1.3, ICAO 3.1.3, IMDG 2.3.1.3, ADR 2.2.3.1.1 Note 1); or others as allowed under hazardous materials/dangerous goods regulations.*

## Section 15: REGULATORY INFORMATION

### International Inventories

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

All components are listed or exempt from listing.

**DSL** - Canadian Domestic Substances List

Not all components are listed or exempt from listing

### US Federal Regulations

Chemical Name	SARA 313 - Threshold Values %	Metals	Hazardous air pollutants (HAPs) content
Chlorothalonil 1897-45-6 0.3 - 1	0.1		

**SARA 311/312 Hazard Categories**

Acute health hazard	Yes
Chronic Health Hazard	Yes
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

Chemical Name	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Diuron 330-54-1	100 lb			X

Chemical Name	Hazardous Substances RQs	CERCLA/SARA RQ	Reportable Quantity (RQ)
Carbamic acid, 1H-benzimidazol-2-yl-, methyl ester 10605-21-7	10 lb		RQ 10 lb final RQ RQ 4.54 kg final RQ
Diuron 330-54-1	100 lb		RQ 100 lb final RQ RQ 45.4 kg final RQ

**US State Regulations**

**Rule 66 status of product**

Not photochemically reactive.

**California Proposition 65**

WARNING! This product contains a chemical known in the State of California to cause cancer.

**U.S. EPA Label information**

EPA Pesticide registration number Not applicable

**U.S. State Right-to-Know Regulations**

Chemical Name
Water 7732-18-5
Proprietary Non-Hazardous Ingredient - Proprietary CAS
Proprietary Inert
Limestone 1317-65-3
Inorganic Inert
Kaolin 1332-58-7
Titanium dioxide 13463-67-7
1,2-Propylene glycol 57-55-6
Chlorothalonil 1897-45-6
Carbamic acid, 1H-benzimidazol-2-yl-, methyl ester 10605-21-7
Quartz 14808-60-7
Diuron



**Section 16: OTHER INFORMATION****HMIS****Health hazards** 2\*

\* = Chronic Health Hazard

**Flammability** 1**Physical hazards** 0**Personal Protection** X**Supplier Address**

Valspar Consumer Headquarters 8725 W. Higgins Rd. Suite 1000 Chicago, IL 60631 773-628-5500	The Valspar Corporation 4999 36th St. Grand Rapids, MI 49512 800-253-3957	Valspar Plasti-Kote 1636 Shawson Dr. Mississauga, Ontario L4W 1N7 905-671-8333
--	--	---

**Prepared By** Product Stewardship**Revision date** 02-Mar-2018**Revision Note** No information available**Disclaimer**

The information on this Safety Data Sheet (SDS) is based on the present state of our knowledge, current national legislation and guidelines. As the specific conditions of use of the product are outside the supplier's knowledge and control the user is responsible for ensuring that the requirements of relevant legislation are complied with. This SDS should not be construed as any guarantee of the technical performance or suitability for particular applications. **UNLESS SUPPLIER AGREES OTHERWISE IN WRITING, SUPPLIER MAKES NO WARRANTIES, EXPRESS OR IMPLIED, AND DISCLAIMS ALL IMPLIED WARRANTIES INCLUDING WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR USE OR FREEDOM FROM PATENT INFRINGEMENT. SUPPLIER WILL NOT BE LIABLE FOR ANY SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES.**

**End of Safety Data Sheet**