

# SAFETY DATA SHEET

according to 29 CFR 1910.1200 and ANSI standard Z400.1-2010



## Wood files and rasps

Product number 171

Revision date: Mar/14/2019  
Version: 6

Language: en-US,CA

Date of print: Oct/8/2019  
Page: 1 of 11

### 1. Product and company identification

#### Product identifier

Trade name: Wood files and rasps  
This safety data sheet pertains to the following products:  
Wood rasps  
Wood files  
Hoof rasps  
File rasps

#### Relevant identified uses of the substance or mixture and uses advised against

General use: Tools for surface treatment of various woods.  
For industrial purposes only

#### Details of the supplier of the safety data sheet

Company name:  
PFERD INC.  
Street/POB-No.: 9201 W. Heather Ave.  
Postal Code, city: Milwaukee, WI 53224,  
USA  
WWW: [www.pferdusa.com](http://www.pferdusa.com)  
E-mail: [sales@pferdusa.com](mailto:sales@pferdusa.com)  
Telephone: 1-800-342-9015  
Telefax: 262-255-2840  
Department responsible for information:  
1-800-342-9015

PFERD CANADA INC.  
Street/POB-No.: 5570 McAdam Road  
Postal Code, city: Mississauga, Ontario L4Z 1P1,  
Canada  
WWW: [www.pferdusa.com](http://www.pferdusa.com)  
E-mail: [sales@pferdcanada.ca](mailto:sales@pferdcanada.ca)  
Telephone: (905) 501-1555  
Telefax: (905) 501-1554  
Department responsible for information: 1-866-245-1555

#### Emergency phone number

USA/Canada: 1-800-255-3924

### 2. Hazards identification

#### Emergency overview

Appearance: Form: solid  
Color: gray  
Odor: odorless  
Classification: Sensitization - skin - Category 1; Carcinogenicity - Category 2;  
Hazard symbols:



Signal word: **Warning**  
Hazard statements: May cause an allergic skin reaction.  
Suspected of causing cancer.

# SAFETY DATA SHEET

according to 29 CFR 1910.1200 and ANSI standard Z400.1-2010



## Wood files and rasps

Product number 171

Revision date: Mar/14/2019  
Version: 6

Language: en-US,CA

Date of print: Oct/8/2019  
Page: 2 of 11

### Precautionary statements:

Obtain special instructions before use.  
Avoid breathing dust/fume/gas/mist/vapors/spray.  
Contaminated work clothing should not be allowed out of the workplace.  
Wear protective gloves/protective clothing/eye protection/face protection.  
IF ON SKIN: Wash with plenty of water/soap.  
IF exposed or concerned: Get medical advice/attention.  
Specific treatment (see ' First aid ' on this label).  
If skin irritation or rash occurs: Get medical advice/attention.  
Wash contaminated clothing before reuse.  
Store locked up.  
Dispose of contents/container to hazardous or special waste collection point.

### Additional information

The hazard identification is based on a formalistic procedure as the hazard statements of the ingredients are summarized under section 3. This does not correspond to the hazardousness of the product itself. A greater hazard, in most cases, is the exposure to the dust/fumes from the wood material or paint/coatings being filed. Most of the dust generated during filing is from the base material being filed and the potential hazard from this exposure must be evaluated. This dust may present a fire or dust explosion hazard and may present a serious health hazard.

### Regulatory status

This material is considered hazardous by the U.S. OSHA Hazard Communication Standard (29 CFR 1910.1200) and WHMIS in Canada.

### Hazards not otherwise classified

Mechanical processing can produce particles and dust.  
Inhalation of dust may cause irritation of the respiratory system.  
Dust contact with the eyes can lead to mechanical irritation.  
see section 11: Toxicological information

## 3. Composition / Information on ingredients

### Relevant ingredients:

CAS No.	Designation	Content	Classification
CAS 7439-89-6	Iron	< 98 %	not classified
CAS 7440-44-0	Carbon	< 2 %	not classified
CAS 7440-47-3	Chromium	< 1 %	not classified
CAS 7439-96-5	Manganese	< 1 %	not classified
CAS 7440-21-3	Silicon	< 1 %	not classified
CAS 7439-98-7	Molybdenum	< 1 %	not classified
CAS 7440-02-0	Nickel	< 1 %	Sensitization - skin - Category 1. Carcinogenicity - Category 2. Specific Target Organ Toxicity (Repeated Exposure) - Category 1. Aquatic toxicity - chronic - Category 3.
CAS 7723-14-0	Phosphorus	< 0.1 %	not classified
CAS 7704-34-9	Sulfur	< 0.1 %	Skin Irritation - Category 2.

Additional information: The specific identity and/or exact percentage has been withheld as a trade secret.

# SAFETY DATA SHEET

according to 29 CFR 1910.1200 and ANSI standard Z400.1-2010



## Wood files and rasps

Product number 171

Revision date: Mar/14/2019  
Version: 6

Language: en-US,CA

Date of print: Oct/8/2019  
Page: 3 of 11

### 4. First aid measures

- In case of inhalation: Provide fresh air. If you feel unwell, seek medical advice.
- Following skin contact: Remove residues with soap and water. Take off contaminated clothing and wash it before reuse. In case of skin reactions, consult a physician.
- After eye contact: Immediately flush eyes with plenty of flowing water for 10 to 15 minutes holding eyelids apart. In case of eye irritation consult an ophthalmologist.
- After swallowing: Rinse mouth with water. Seek medical attention.

#### Most important symptoms/effects, acute and delayed

May cause an allergic skin reaction.

#### Information to physician

Treat symptomatically.

### 5. Fire fighting measures

Flash point/flash point range:

No data available

Auto-ignition temperature: No data available

Suitable extinguishing media:

Product is non-combustible. Extinguishing materials should therefore be selected according to surroundings.

#### Specific hazards arising from the chemical

On heating or in case of fire toxic gases may form.

Protective equipment and precautions for firefighters:

Wear self-contained breathing apparatus. Wear suitable protective clothing.

Additional information:

Do not allow fire water to penetrate into surface or ground water.

### 6. Accidental release measures

Personal precautions:

Avoid generation of dust. Do not inhale substance.  
Provide adequate ventilation. Wear appropriate protective equipment.  
Avoid contact with the substance. Keep unprotected people away.

Environmental precautions:

Do not allow to penetrate into soil, waterbodies or drains.  
In case of release, notify competent authorities.

Methods for clean-up:

Take up mechanically, placing in appropriate containers for disposal.

# SAFETY DATA SHEET

according to 29 CFR 1910.1200 and ANSI standard Z400.1-2010



## Wood files and rasps

Product number 171

Revision date: Mar/14/2019

Version: 6

Language: en-US,CA

Date of print: Oct/8/2019

Page: 4 of 11

## 7. Handling and storage

### Handling

Advices on safe handling: Provide adequate ventilation, and local exhaust as needed.

Avoid generation of dust. Do not inhale substance.

Wear appropriate protective equipment.

When using do not eat, drink or smoke.

Wash hands before breaks and after work.

Obtain special instructions before use.

### Storage

Requirements for storerooms and containers:

Store container tightly closed in a dry area.

Protect from moisture contamination.

# SAFETY DATA SHEET

according to 29 CFR 1910.1200 and ANSI standard Z400.1-2010



## Wood files and rasps

Product number 171

Revision date: Mar/14/2019  
Version: 6

Language: en-US,CA

Date of print: Oct/8/2019  
Page: 5 of 11

### 8. Exposure controls / personal protection

#### Exposure guidelines

Occupational exposure limit values:

CAS No.	Designation	Type	Limit value
7439-89-6	Iron	USA: ACGIH: TWA	10 mg/m <sup>3</sup> (smoke, dust)
		USA: OSHA: TWA	10 mg/m <sup>3</sup> (Smoke)
7440-44-0	Carbon	Canada, Alberta: OEL 8 hour	10 mg/m <sup>3</sup> (Dust limit value, inhalable fraction)
		Canada, Alberta: OEL 8 hour	3 mg/m <sup>3</sup> (Dust limit value, respirable fraction)
		Canada, BC: OEL TWA	10 mg/m <sup>3</sup> (Dust limit value, inhalable fraction)
		Canada, Ontario: OEL TWA	10 mg/m <sup>3</sup> (Dust limit value, inhalable fraction)
		Canada, Ontario: OEL TWA	3 mg/m <sup>3</sup> (Dust limit value, respirable fraction)
		Canada, Québec: VEMP	10 mg/m <sup>3</sup> (Dust limit value, inhalable fraction)
		USA: ACGIH: TWA	10 mg/m <sup>3</sup> (Dust limit value, inhalable fraction)
		USA: ACGIH: TWA	3 mg/m <sup>3</sup> (Dust limit value, respirable fraction)
		USA: OSHA: TWA	15 mg/m <sup>3</sup> inhalable fraction
		USA: OSHA: TWA	5 mg/m <sup>3</sup> (respirable fraction)
7440-47-3	Chromium	Canada, Alberta: OEL 8 hour	0.5 mg/m <sup>3</sup>
		Canada, BC: OEL TWA	0.5 mg/m <sup>3</sup>
		Canada, Québec: VEMP	0.5 mg/m <sup>3</sup>
		USA: ACGIH: TWA	0.5 mg/m <sup>3</sup> (inhalable fraction)
		USA: NIOSH: TWA	0.5 mg/m <sup>3</sup>
7439-96-5	Manganese	USA: OSHA: TWA	0.5 mg/m <sup>3</sup>
		Canada, Alberta: OEL 8 hour	0.2 mg/m <sup>3</sup>
		Canada, BC: OEL TWA	0.02 mg/m <sup>3</sup> (inhalable fraction)
		Canada, BC: OEL TWA	0.2 mg/m <sup>3</sup> (respirable fraction)
7440-21-3	Silicon	Canada, Québec: VEMP	0.2 mg/m <sup>3</sup> (Smoke, inhalable fraction)
		Canada, Ontario: OEL TWA	10 mg/m <sup>3</sup>
		Canada, Québec: VEMP	10 mg/m <sup>3</sup> (inhalable fraction)
		USA: NIOSH: TWA	10 mg/m <sup>3</sup> inhalable fraction
		USA: NIOSH: TWA	5 mg/m <sup>3</sup> (respirable fraction)
		USA: OSHA: TWA	15 mg/m <sup>3</sup> inhalable fraction
		USA: OSHA: TWA	5 mg/m <sup>3</sup> (respirable fraction)

# SAFETY DATA SHEET

according to 29 CFR 1910.1200 and ANSI standard Z400.1-2010



## Wood files and rasps

Product number 171

Revision date: Mar/14/2019  
Version: 6

Language: en-US,CA

Date of print: Oct/8/2019  
Page: 6 of 11

CAS No.	Designation	Type	Limit value
7439-98-7	Molybdenum	Canada, Alberta: OEL 8 hour	0.5 mg/m <sup>3</sup> compounds, soluble; respirable fraction
		Canada, Alberta: OEL 8 hour	10 mg/m <sup>3</sup> (Metal insoluble compounds total)
		Canada, Alberta: OEL 8 hour	3 mg/m <sup>3</sup> (metal, compounds, insoluble; respirable fraction)
		Canada, BC: OEL TWA	0.5 mg/m <sup>3</sup> compounds, soluble; respirable fraction
		Canada, BC: OEL TWA	10 mg/m <sup>3</sup> metal and compounds, insoluble; inhalable fraction
		Canada, BC: OEL TWA	3 mg/m <sup>3</sup> metal and compounds, insoluble; respirable fraction
		Canada, Québec: VEMP	10 mg/m <sup>3</sup> compounds, insoluble
		Canada, Québec: VEMP	5 mg/m <sup>3</sup> compounds, soluble
		USA: ACGIH: TWA	0.5 mg/m <sup>3</sup> soluble; inhalable fraction
		USA: ACGIH: TWA	10 mg/m <sup>3</sup> insoluble; inhalable fraction
		USA: ACGIH: TWA	3 mg/m <sup>3</sup> insoluble; respirable fraction
		USA: OSHA: TWA	15 mg/m <sup>3</sup>
		USA: OSHA: TWA	5 mg/m <sup>3</sup>
7440-02-0	Nickel	Canada, Alberta: OEL 8 hour	1.5 mg/m <sup>3</sup> (metal)
		Canada, BC: OEL TWA	0.05 mg/m <sup>3</sup>
		Canada, Ontario: OEL TWA	1 mg/m <sup>3</sup> (metal, inhalable fraction)
		Canada, Québec: VEMP	1 mg/m <sup>3</sup> (metal)
		USA: ACGIH: TWA	1.5 mg/m <sup>3</sup> (metal, inhalable fraction)
		USA: NIOSH: TWA	0.015 mg/m <sup>3</sup>
		USA: OSHA: TWA	1 mg/m <sup>3</sup> (Nickel and compounds)
7723-14-0	Phosphorus	Canada, Alberta: OEL 8 hour	0.1 mg/m <sup>3</sup>
		Canada, Québec: VEMP	0.1 mg/m <sup>3</sup>
		USA: NIOSH: TWA	0.1 mg/m <sup>3</sup>
7704-34-9	Sulfur	Canada, Alberta: OEL 8 hour	10 mg/m <sup>3</sup>

### Engineering controls

Provide good ventilation and/or an exhaust system in the work area.  
See also information in chapter 7, section storage.

### Personal protection equipment (PPE)

Eye/face protection: Tightly sealed goggles according to OSHA Standard - 29 CFR: 1910.133 or ANSI Z87.1-2010.

Skin protection: Wear suitable protective clothing and shoes.  
Protective gloves according to OSHA Standard - 29 CFR: 1910.138.

Respiratory protection: Respiratory protection must be worn whenever the TLV (WEL) levels have been exceeded. The filter class must be suitable for the maximum contaminant concentration (gas/vapour/aerosol/particulates) that may arise when handling the product. If the concentration is exceeded, self-contained breathing apparatus must be used.

# SAFETY DATA SHEET

according to 29 CFR 1910.1200 and ANSI standard Z400.1-2010



## Wood files and rasps

Product number 171

Revision date: Mar/14/2019  
Version: 6

Language: en-US,CA

Date of print: Oct/8/2019  
Page: 7 of 11

General hygiene considerations:

- Do not inhale substance.
- Avoid contact with skin and eyes.
- When using do not eat, drink or smoke. Change contaminated clothing.
- Wash hands before breaks and after work.
- Work place should be equipped with a shower and an eye rinsing apparatus.
- Obtain special instructions before use.

## 9. Physical and chemical properties

### Information on basic physical and chemical properties

Appearance:	Form: solid Color: gray
Odor:	odorless
Odor threshold:	No data available
pH value:	No data available
Melting point/freezing point:	No data available
Initial boiling point and boiling range:	No data available
Flash point/flash point range:	No data available
Evaporation rate:	No data available
Flammability:	No data available
Explosion limits:	No data available
Vapor pressure:	No data available
Vapor density:	No data available
Density:	No data available
Solubility:	No data available
Partition coefficient: n-octanol/water:	No data available
Auto-ignition temperature:	No data available
Thermal decomposition:	No data available
Additional information:	No data available

## 10. Stability and reactivity

Reactivity:	Mechanical processing can produce particles and dust. The product in the delivered form is not dust explosion capable; the enrichment of fine dust however leads to the danger of dust explosion.
Chemical stability:	Stable under recommended storage conditions.
Possibility of hazardous reactions:	No hazardous reaction when handled and stored according to provisions.
Conditions to avoid:	No data available
Incompatible materials:	No data available

# SAFETY DATA SHEET

according to 29 CFR 1910.1200 and ANSI standard Z400.1-2010



## Wood files and rasps

Product number 171

Revision date: Mar/14/2019  
Version: 6

Language: en-US,CA

Date of print: Oct/8/2019  
Page: 8 of 11

Hazardous decomposition products:

On heating or in case of fire toxic gases may form.

Thermal decomposition: No data available

## 11. Toxicological information

### Toxicological tests

Toxicological effects: The statements are derived from the properties of the single components. No toxicological data is available for the product as such.

Acute toxicity (oral): Based on available data, the classification criteria are not met.

Acute toxicity (dermal): Based on available data, the classification criteria are not met.

Acute toxicity (inhalative): Based on available data, the classification criteria are not met.

Skin corrosion/irritation: Based on available data, the classification criteria are not met.

Serious eye damage/irritation: Based on available data, the classification criteria are not met.

Sensitisation to the respiratory tract: Based on available data, the classification criteria are not met.

Skin sensitisation: Sensitization - skin -

Category 1 = May cause an allergic skin reaction. May cause sensitisation especially in sensitive humans.

Germ cell mutagenicity/Genotoxicity: Based on available data, the classification criteria are not met.

Carcinogenicity: Carcinogenicity - Category 2 = Suspected of causing cancer.

Reproductive toxicity: Based on available data, the classification criteria are not met.

Effects on or via lactation: Based on available data, the classification criteria are not met.

Specific target organ toxicity (single exposure): Based on available data, the classification criteria are not met.

Specific target organ toxicity (repeated exposure): Based on available data, the classification criteria are not met.

Aspiration hazard: Based on available data, the classification criteria are not met.

Other information: Chronic toxicity carcinogenic effect:

Information about Nickel:

IARC Rating: Group 2B

OSHA Carcinogen: not listed

NTP Rating: listed

Information about Chromium:

IARC Rating: Group 3

OSHA Carcinogen: not listed

NTP Rating: not listed

### Symptoms

In case of inhalation: Inhalation of dust may cause irritation of the respiratory system.

Lung damage is possible in a chronic situation. Cough, shortage of breath.

After contact with skin: In the case of the formation of dust: May cause irritations.

After eye contact: Dust contact with the eyes can lead to mechanical irritation.



# SAFETY DATA SHEET

according to 29 CFR 1910.1200 and ANSI standard Z400.1-2010



## Wood files and rasps

Product number 171

Revision date: Mar/14/2019  
Version: 6

Language: en-US,CA

Date of print: Oct/8/2019  
Page: 9 of 11

## 12. Ecological information

### Ecotoxicity

Further details: No data available

### Mobility in soil

No data available

### Persistence and degradability

Further details: No data available

### Additional ecological information

General information: Do not allow to enter into ground-water, surface water or drains.

## 13. Disposal considerations

### Product

Recommendation: Dispose of waste according to applicable legislation.

### Contaminated packaging

Recommendation: Dispose of waste according to applicable legislation. Packing can be recycled or disposed of.

## 14. Transport information

### USA: Department of Transportation (DOT)

Proper shipping name: Not restricted

### Canada: Transportation of Dangerous Goods (TDG)

Shipping name: Not restricted

### Sea transport (IMDG)

Proper shipping name: Not restricted

Marine pollutant: no

### Air transport (IATA)

Proper shipping name: Not restricted

### Further information

No dangerous good in sense of these transport regulations.

# SAFETY DATA SHEET

according to 29 CFR 1910.1200 and ANSI standard Z400.1-2010



## Wood files and rasps

Product number 171

Revision date: Mar/14/2019  
Version: 6

Language: en-US,CA

Date of print: Oct/8/2019  
Page: 10 of 11

### 15. Regulatory information

#### National regulations - U.S. Federal Regulations

Product:	This product is an article as defined by TSCA regulations, and is exempt from TSCA inventory listing requirements.
Carbon:	NIOSH Recommendations: Occupational Health Guideline: 0307
Chromium:	Carcinogen Status: IARC Rating: Group 3 OSHA Carcinogen: not listed NTP Rating: not listed Clean Water Act: Priority Pollutant: yes Other Environmental Laws: CERCLA: RQ 5000 lbs. RCRA Hazardous Wastes: Code D007 RCRA Groundwater Monitoring: Methods 6010, 7190, 719 / PQL 70, 500, 10 SARA Title III Section 313, Toxic Release: Conc. 0.1% / Threshold Standard NIOSH Recommendations: Occupational Health Guideline: 0141
Manganese:	Other Environmental Laws: SARA Title III Section 313, Toxic Release: Conc. 1.0% / Threshold Standard NIOSH Recommendations: Occupational Health Guideline: 0379*
Silicon:	NIOSH Recommendations: Occupational Health Guideline: 0554
Molybdenum:	NIOSH Recommendations: Occupational Health Guideline: 0433*
Nickel:	Carcinogen Status: IARC Rating: Group 2B OSHA Carcinogen: not listed NTP Rating: listed Clean Water Act: Priority Pollutant: yes Other Environmental Laws: CERCLA: RQ 100* lbs. RCRA Groundwater Monitoring: Methods 6010, 7520 / PQL 50, 400 SARA Title III Section 313, Toxic Release: Conc. 0.1% / Threshold Standard NIOSH Recommendations: Occupational Health Guideline: 0445*

# SAFETY DATA SHEET

according to 29 CFR 1910.1200 and ANSI standard Z400.1-2010



## Wood files and rasps

Product number 171

Revision date: Mar/14/2019  
Version: 6

Language: en-US,CA

Date of print: Oct/8/2019  
Page: 11 of 11

Phosphorus:

Clean Air Act:  
Hazardous Air Pollutants: Code X

Clean Water Act:  
Hazardous Substances: RQ 1 lbs.

Other Environmental Laws:  
CERCLA: RQ 1 lbs.  
Marine Pollutant: listed as severe pollutant.  
SARA Title III Section 302, EHS: TPQ 100 lbs. / RQ 1 lbs.  
SARA Title III Section 313, Toxic Release: Conc. 1.0% / Threshold Standard

NIOSH Recommendations:  
Occupational Health Guideline: 0507

### National regulations - U.S. State Regulations

Nickel: California Proposition 65: cancer

### National regulations - Canada

No data available

## 16. Other information

Hazard rating systems:



NFPA Hazard Rating:  
Health: 2 (Moderate)  
Fire: 0 (Minimal)  
Reactivity: 0 (Minimal)

HMIS Version III Rating:  
Health: 2 (Moderate) - Chronic effects  
Flammability: 0 (Minimal)  
Physical Hazard: 0 (Minimal)  
Personal Protection: X = Consult your supervisor

HEALTH	*	2
FLAMMABILITY		0
PHYSICAL HAZARD		0
		X

Reason of change: General revision

Date of first version: Feb/3/2016

### Department issuing data sheet

Contact person: see section 1: Department responsible for information

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products.